



Accessories for Retail Display Lighting Modules and Drivers

Accessories

Drivers and accessories that allow true system proposition

Features

- Cables
- Clips
- Profiles
- Track System
- Others

Application

- True system proposition with Integrate G4 modules and constant voltage Drivers.
- True system proposition with Integrate S modules and constant voltage Drivers.
- True system proposition with CertaFlux modules and constant voltage Drivers.

Versions














Clip Shelf Arm













IntegrateS Mounting Profile 1200

Versions

	InteGrade engine clip mullion center		InteGrade engine lock inline
	InteGrade track cable 0.4mT		InteGrade spacer cable 0.3m black
	InteGrade track cable 0.5mT		InteGrade profile 2000mm
	InteGrade mounting clip canopy		Fortimo LEDFlex connector
	InteGrade profile 2000mm 79 Tstyle CTR		InteGrade engine clip mullion side
			IntegradeS Mounting Profile 900



Accessories

Versions

	InteGrade power cable 1m black		InteGrade cable 2.5m black
	InteGrade snap in clip		InteGrade track 1200mm G
			InteGrade profile 1175mm
	Fortimo LEDFlex connector wire250mm		InteGrade spacer cable 113mm white
			InteGrade engin mounting clip G2
	InteGrade connector		InteGrade spacer cable 0.5m white

Accessories

Versions

	Fortimo LEDFlex cornerconnect wire150mm		InteGrade power cable 2.5m white
	InteGrade profile 2000mm Fstyle		Clip Cannopy 30
	Fortimo LEDFlex connector wire2000mm		InteGrade mounting clip under shelf
	InteGrade cable 2.5m white		Clip Cannopy 0
	InteGrade rotational bracket		InteGrade cable 1m black
	InteGrade engine clip magnetic		InteGrade power cable 6m white

Accessories

Versions



InteGrade power cable 1m white



InteGrade mounting clip Tstyle profile



InteGrade mounting clip Tstyle profile



Fortimo LEDFlex connector wire500mm



InteGrade profile 2000mm 79 Tstyle SD



InteGrade profile 2000mm 79 Tstyle SD



InteGrade profile 2000mm 79 Tstyle SD




IntegradeS Mounting Clip



InteGrade spacer cable 0.5m black



Clip Shelf Front



InteGrade cable 1m white



InteGrade screw clip Tstyle prof



InteGrade track 600mm G

Accessories

Versions



InteGrade profile 875mm



Fortimo LEDFlex cornerconnect
wire60mm



InteGrade spacer cable M0 7m5 5c
black




InteGrade magnet Mstyle profile




Clip Shelf Magnetic

Dimensional drawing




Product	C1	A1	B1
InteGrade profile 1175mm(46")	11.9 mm	1,175.0 mm	22.2 mm
InteGrade profile 2000mm(79")	11.9 mm	2,000.0 mm	22.2 mm
InteGrade profile 875mm(34")	11.9 mm	875.0 mm	22.2 mm



Product	C1	A1	B1	B2
InteGrade profile 2000mm(79") F style	11.9 mm	2,000.0 mm	31.0 mm	26.0 mm

Dimensional drawing

Image
not yet
available



Product				
InteGrade magnet for M style profile				


Product	A1	B1	C1	D1
InteGrade engine lock inline	18.7 mm	10 mm	10.7 mm	4.2 mm

Product	A1	B1	C1	D1
InteGrade mounting clip for T style prof	66.5 mm	19.5 mm	5 mm	4.2 mm


Product	A
InteGrade cable 1m(39") black angle	1,000 mm
InteGrade cable 1m(39") white angle	1,000 mm
InteGrade cable 2.5m(98") black angle	2,500 mm
InteGrade cable 2.5m(98") white angle	2,500 mm

Accessories


Dimensional drawing



Product	A
InteGrade spacer cable 0.5m black	500 mm
InteGrade spacer cable 0.5m white	500 mm



Product	A
InteGrade power cable 1m(39") black	1,000 mm
InteGrade power cable 1m(39") white	1,000 mm
InteGrade power cable 2.5m(98") black	2,500 mm
InteGrade power cable 2.5m(98") white	2,500 mm



Product	C1	A1	B1
InteGrade mounting clip under shelf	12.5 mm	47.0 mm	30.5 mm

