



Accessories for Retail Display Lighting Modules and Drivers

Accessories

Drivers and accessories that allow true system proposition

Features

- Cables
- Clips
- Profiles
- Track System
- Others

Application

- True system proposition with Integrate G4 modules and constant voltage Drivers.
- True system proposition with Integrate S modules and constant voltage Drivers.
- True system proposition with CertaFlux modules and constant voltage Drivers.

Versions





Clip Shelf Arm



IntegrateS Mounting Profile 1200

Versions

	InteGrade engine lock inline		InteGrade spacer cable 0.3m black
			InteGrade track cable 0.5mT
	InteGrade profile 2000mm		InteGrade mounting clip canopy
	Fortimo LEDFlex connector		InteGrade track cable 0.7mG
			InteGrade track 1800mm G
	IntegrateS Mounting Profile 900		InteGrade power cable 1m black

Accessories

Versions



InteGrade cable 2.5m black




Fortimo LEDFlex connector
wire250mm



InteGrade connector




InteGrade power cable 2.5m white




InteGrade track 1200mm G



InteGrade profile 1175mm




InteGrade engin mounting clip G2



InteGrade spacer cable 0.5m white













Fortimo LEDFlex cornerconnect
wire150mm



InteGrade profile 2000mm Fstyle

Accessories

Versions

	Clip Canopy 30		Fortimo LEDFlex connector wire2000mm
			InteGrade mounting clip under shelf
	InteGrade cable 2.5m white		Clip Canopy 0
	InteGrade power cable 2.5m black		InteGrade cable 1m black
	InteGrade engine clip magnetic		InteGrade power cable 6m white
			InteGrade power cable 1m white

Versions

IntegrateS Mounting Clip




InteGrade mounting clip Tstyle profile



InteGrade spacer cable 0.5m black



Clip Shelf Front



Fortimo LEDFlex connector wire500mm



InteGrade cable 1m white



InteGrade track power cable 1.5m G



InteGrade profile 875mm



Fortimo LEDFlex cornerconnect wire60mm



InteGrade magnet Mstyle profile




Versions


Clip Shelf Magnetic



Dimensional drawing



Product	C1	A1	B1
InteGrade profile 1175mm(46")	11.9 mm	1,175.0 mm	22.2 mm
InteGrade profile 2000mm(79")	11.9 mm	2,000.0 mm	22.2 mm
InteGrade profile 875mm(34")	11.9 mm	875.0 mm	22.2 mm




Product	C1	A1	B1	B2
InteGrade profile 2000mm(79") F style	11.9 mm	2,000.0 mm	31.0 mm	26.0 mm

Image
not yet
available

Product
InteGrade magnet for M style profile

Dimensional drawing



Product	A1	B1	C1	D1
InteGrade engine lock inline	18.7 mm	10 mm	10.7 mm	4.2 mm


Product	A1	B1	C1	D1
InteGrade mounting clip for T style prof	66.5 mm	19.5 mm	5 mm	4.2 mm

Product	A
InteGrade cable 1m(39") black angle	1,000 mm
InteGrade cable 1m(39") white angle	1,000 mm
InteGrade cable 2.5m(98") black angle	2,500 mm
InteGrade cable 2.5m(98") white angle	2,500 mm


Product	A
InteGrade spacer cable 0.5m black	500 mm
InteGrade spacer cable 0.5m white	500 mm

Accessories

Dimensional drawing



Product	A
InteGrade power cable 1m(39") black	1,000 mm
InteGrade power cable 1m(39") white	1,000 mm
InteGrade power cable 2.5m(98") black	2,500 mm
InteGrade power cable 2.5m(98") white	2,500 mm



Product	C1	A1	B1
InteGrade mounting clip under shelf	12.5 mm	47.0 mm	30.5 mm

