



Accesorios para módulos y controladores de iluminación de expositores de venta minorista

Accessories

Controladores y accesorios que permiten una verdadera propuesta de sistema

Características

- Cables
- Clips
- Perfiles
- Sistema de carril
- Otros

Aplicaciones

- Verdadera propuesta de sistema con módulos Integrate G4 y controladores de voltaje constante.
- Verdadera propuesta de sistema con módulos Integrate S y controladores de voltaje constante.
- Verdadera propuesta de sistema con módulos CertaFlux y controladores de voltaje constante.

Accessories


Versions



Clip Shelf Arm




InteGradeS Mounting Profile 1200



InteGrade engine lock inline



InteGrade spacer cable 0.3m black



InteGrade profile 2000mm



InteGrade mounting clip canopy



Fortimo LEDFlex connector



InteGrade profile 2000mm 79
Tstyle CTR



InteGradeS Mounting Profile 900



InteGrade power cable 1m black

Accessories


Versions



InteGrade cable 2.5m black



InteGrade snap in clip




InteGrade profile 1175mm



Fortimo LEDFlex connector
wire250mm



InteGrade spacer cable 113mm
white



InteGrade engin mounting clip G2



InteGrade connector



InteGrade spacer cable 0.5m white







Fortimo LEDFlex cornerconnect
wire150mm



InteGrade power cable 2.5m white

Versions

	InteGrade profile 2000mm Fstyle		Clip Cannopy 30
	Fortimo LEDFlex connector wire2000mm		InteGrade mounting clip under shelf
	InteGrade cable 2.5m white		Clip Cannopy 0
	InteGrade power cable 2.5m black		InteGrade cable 1m black
	InteGrade engine clip magnetic		InteGrade power cable 6m white
			InteGrade power cable 1m white

Versions

IntegrateS Mounting Clip




Integrate mounting clip Tstyle profile



Integrate spacer cable 0.5m black



Clip Shelf Front



Fortimo LEDFlex connector wire500mm



Integrate cable 1m white



Integrate profile 2000mm 79 Tstyle SD



Integrate screw clip Tstyle prof



Integrate profile 875mm




Versions



Fortimo LEDFlex cornerconnect
wire60mm




InteGrade magnet Mstyle profile




Clip Shelf Magnetic

Plano de dimensiones




Product	C1	A1	B1
InteGrade profile 1175mm(46")	11,9 mm	1.175,0 mm	22,2 mm
InteGrade profile 2000mm(79")	11,9 mm	2.000,0 mm	22,2 mm
InteGrade profile 875mm(34")	11,9 mm	875,0 mm	22,2 mm



Product	C1	A1	B1	B2
InteGrade profile 2000mm(79") F style	11,9 mm	2.000,0 mm	31,0 mm	26,0 mm

Plano de dimensiones

Image
not yet
available




Product
InteGrade magnet for M style profile

Product	A1	B1	C1	D1
InteGrade engine lock inline	18,7 mm	10 mm	10,7 mm	4,2 mm


Product	A1	B1	C1	D1
InteGrade mounting clip for T style prof	66,5 mm	19,5 mm	5 mm	4,2 mm

Product	A
InteGrade cable 1m(39") black angle	1.000 mm
InteGrade cable 1m(39") white angle	1.000 mm
InteGrade cable 2.5m(98") black angle	2.500 mm
InteGrade cable 2.5m(98") white angle	2.500 mm


Plano de dimensiones



Product	A
InteGrade spacer cable 0.5m black	500 mm
InteGrade spacer cable 0.5m white	500 mm



Product	A
InteGrade power cable 1m(39") black	1.000 mm
InteGrade power cable 1m(39") white	1.000 mm
InteGrade power cable 2.5m(98") black	2.500 mm
InteGrade power cable 2.5m(98") white	2.500 mm



Product	C1	A1	B1
InteGrade mounting clip under shelf	12,5 mm	47,0 mm	30,5 mm

