



Tartozékok kiskereskedelmi kirakatvilágítási modulokhoz és előtétetekhez

Accessories

Teljes rendszerré kiegészítő előtétetek és tartozékok

Szolgáltatások

- Kábelek
- Kapcsok
- Profilok
- Sínrendszer
- Egyéb

Alkalmazás

- Teljes rendszer Integrate G4 modulokkal és állandó feszültségű előtétetekkel.
- Teljes rendszer Integrate S modulokkal és állandó feszültségű előtétetekkel.
- Teljes rendszer CertaFlux modulokkal és állandó feszültségű előtétetekkel.


Versions



Clip Shelf Arm



InteGradeS Mounting Profile 1200




InteGrade engine lock inline




InteGrade spacer cable 0.3m black



InteGrade track cable 0.5mT



InteGrade profile 2000mm



InteGrade mounting clip canopy





InteGrade track 1800mm G




InteGradeS Mounting Profile 900

Versions

	InteGrade power cable 1m black		InteGrade cable 2.5m black
	InteGrade track 1200mm G		InteGrade profile 1175mm
	InteGrade engin mounting clip G2		InteGrade connector
	InteGrade spacer cable 0.5m white		InteGrade power cable 2.5m white
	InteGrade profile 2000mm Fstyle		Clip Cannopy 30
	InteGrade mounting clip under shelf		InteGrade cable 2.5m white

Accessories

Versions



Clip Canopy 0



InteGrade power cable 2.5m black



InteGrade power cable 6m white



InteGrade engine clip magnetic




IntegradeS Mounting Clip



InteGrade cable 1m white



InteGrade power cable 1m white



InteGrade mounting clip Tstyle profile

Clip Shelf Front

InteGrade track power cable 1.5m G

Versions



InteGrade profile 875mm




InteGrade magnet Mstyle profile




Clip Shelf Magnetic

Méretezett rajza




Product	C1	A1	B1
InteGrade profile 1175mm(46")	11,9 mm	1 175,0 mm	22,2 mm
InteGrade profile 2000mm(79")	11,9 mm	2 000,0 mm	22,2 mm
InteGrade profile 875mm(34")	11,9 mm	875,0 mm	22,2 mm



Product	C1	A1	B1	B2
InteGrade profile 2000mm(79") F style	11,9 mm	2 000,0 mm	31,0 mm	26,0 mm

Méretezett rajza

Image
not yet
available



Product				
InteGrade magnet for M style profile				


Product	A1	B1	C1	D1
InteGrade engine lock inline	18,7 mm	10 mm	10,7 mm	4,2 mm

Product	A1	B1	C1	D1
InteGrade mounting clip for T style prof	66,5 mm	19,5 mm	5 mm	4,2 mm


Product	A
InteGrade cable 1m(39") white angle	1 000 mm
InteGrade cable 2.5m(98") black angle	2 500 mm
InteGrade cable 2.5m(98") white angle	2 500 mm

Accessories


Méretezett rajza



Product	A
InteGrade spacer cable 0.5m white	500 mm



Product	A
InteGrade power cable 1m(39") black	1 000 mm
InteGrade power cable 1m(39") white	1 000 mm
InteGrade power cable 2.5m(98") black	2 500 mm
InteGrade power cable 2.5m(98") white	2 500 mm



Product	C1	A1	B1
InteGrade mounting clip under shelf	12,5 mm	47,0 mm	30,5 mm

