



# Acessórios para drivers e módulos de iluminação de expositores de revenda

## Accessories

Drivers e acessórios que permitem uma verdadeira proposta do sistema

### Características

- Cabos
- Clips
- Perfis
- Sistema de calhas
- Outros

### Aplicação

- Uma verdadeira proposta de sistema com módulos Integrate G4 e drivers de tensão constante.
- Uma verdadeira proposta de sistema com módulos Integrate S e drivers de tensão constante.
- Uma verdadeira proposta de sistema com módulos CertaFlux e drivers de tensão constante.

Versions




Clip Shelf Arm



InteGradeS Mounting Profile 1200




InteGrade engine lock inline



InteGrade spacer cable 0.3m black



InteGrade profile 2000mm



InteGrade mounting clip canopy



Fortimo LEDFlex connector



InteGrade profile 2000mm 79  
Tstyle CTR



InteGradeS Mounting Profile 900



InteGrade power cable 1m black



Accessories


Versions



InteGrade cable 2.5m black



InteGrade snap in clip



InteGrade profile 1175mm



Fortimo LEDFlex connector  
wire250mm



InteGrade spacer cable 113mm  
white



InteGrade engin mounting clip G2



InteGrade connector



InteGrade spacer cable 0.5m white







Fortimo LEDFlex cornerconnect  
wire150mm



InteGrade power cable 2.5m white

Versions

|                                                                                     |                                      |                                                                                      |                                     |
|-------------------------------------------------------------------------------------|--------------------------------------|--------------------------------------------------------------------------------------|-------------------------------------|
|    | InteGrade profile 2000mm Fstyle      |    | Clip Cannopy 30                     |
|    | Fortimo LEDFlex connector wire2000mm |    | InteGrade mounting clip under shelf |
|    | InteGrade cable 2.5m white           |   | Clip Cannopy 0                      |
|  | InteGrade cable 1m black             |  | InteGrade engine clip magnetic      |
|  | InteGrade power cable 6m white       |  | InteGrade power cable 1m white      |

Versions

IntegrateS Mounting Clip




InteGrade mounting clip Tstyle profile




InteGrade spacer cable 0.5m black



Clip Shelf Front



Fortimo LEDFlex connector wire500mm



InteGrade cable 1m white



InteGrade profile 2000mm 79 Tstyle SD



InteGrade screw clip Tstyle prof



InteGrade profile 875mm



Versions



Fortimo LEDFlex cornerconnect  
wire60mm




InteGrade magnet Mstyle profile




Clip Shelf Magnetic

Desenho dimensional




| Product                       | C1      | A1         | B1      |
|-------------------------------|---------|------------|---------|
| InteGrade profile 1175mm(46") | 11,9 mm | 1.175,0 mm | 22,2 mm |
| InteGrade profile 2000mm(79") | 11,9 mm | 2.000,0 mm | 22,2 mm |
| InteGrade profile 875mm(34")  | 11,9 mm | 875,0 mm   | 22,2 mm |



| Product                               | C1      | A1         | B1      | B2      |
|---------------------------------------|---------|------------|---------|---------|
| InteGrade profile 2000mm(79") F style | 11,9 mm | 2.000,0 mm | 31,0 mm | 26,0 mm |

Desenho dimensional

Image  
not yet  
available



| Product                              |  |  |  |  |
|--------------------------------------|--|--|--|--|
| InteGrade magnet for M style profile |  |  |  |  |


| Product                      | A1      | B1    | C1      | D1     |
|------------------------------|---------|-------|---------|--------|
| InteGrade engine lock inline | 18,7 mm | 10 mm | 10,7 mm | 4,2 mm |

| Product                                  | A1      | B1      | C1   | D1     |
|------------------------------------------|---------|---------|------|--------|
| InteGrade mounting clip for T style prof | 66,5 mm | 19,5 mm | 5 mm | 4,2 mm |


| Product                               | A        |
|---------------------------------------|----------|
| InteGrade cable 1m(39") black angle   | 1.000 mm |
| InteGrade cable 1m(39") white angle   | 1.000 mm |
| InteGrade cable 2.5m(98") black angle | 2.500 mm |
| InteGrade cable 2.5m(98") white angle | 2.500 mm |

Accessories


Desenho dimensional



| Product                           | A      |
|-----------------------------------|--------|
| InteGrade spacer cable 0.5m black | 500 mm |
| InteGrade spacer cable 0.5m white | 500 mm |



| Product                               | A        |
|---------------------------------------|----------|
| InteGrade power cable 1m(39") black   | 1.000 mm |
| InteGrade power cable 1m(39") white   | 1.000 mm |
| InteGrade power cable 2.5m(98") black | 2.500 mm |
| InteGrade power cable 2.5m(98") white | 2.500 mm |



| Product                             | C1      | A1      | B1      |
|-------------------------------------|---------|---------|---------|
| InteGrade mounting clip under shelf | 12,5 mm | 47,0 mm | 30,5 mm |

