



Príslušenstvo pre moduly a napájače prezentačného osvetlenia v maloobchodnom prostredí

Accessories

Napájače a príslušenstvo, ktoré umožňujú využiť ponuku celého systému



Vlastnosti

- Káble
- Svorky
- Profily
- Lištový systém
- Iné





Aplikácie

- Ponuka celého systému s modulmi Integrate G4 a napájačmi s konštantným napätím.
- Ponuka celého systému s modulmi Integrate S a napájačmi s konštantným napätím.
- Ponuka celého systému s modulmi CertaFlux a napájačmi s konštantným napätím.

Versions


	Clip Shelf Arm		InteGradeS Mounting Profile 1200
	InteGrade spacer cable 0.3m black		InteGrade engine lock inline
			InteGrade track cable 0.5mT
			InteGrade profile 2000mm
	InteGrade mounting clip canopy		InteGrade track 1800mm G
			InteGradeS Mounting Profile 900

Versions

	InteGrade power cable 1m black		InteGrade cable 2.5m black
	InteGrade track 1200mm G		InteGrade profile 1175mm
	InteGrade engin mounting clip G2		InteGrade connector
	InteGrade spacer cable 0.5m white		InteGrade power cable 2.5m white
	InteGrade profile 2000mm Fstyle		Clip Cannopy 30
	InteGrade mounting clip under shelf		InteGrade cable 2.5m white

Accessories


Versions



Clip Canopy 0



InteGrade power cable 2.5m black



InteGrade engine clip magnetic



InteGrade power cable 6m white




InteGrade power cable 1m white



InteGradeS Mounting Clip



InteGrade mounting clip Tstyle profile



Clip Shelf Front



InteGrade cable 1m white



InteGrade track power cable 1.5m G

Versions



InteGrade profile 875mm




InteGrade magnet Mstyle profile




Clip Shelf Magnetic

Rozmerový obrázok




Product	C1	A1	B1
InteGrade profile 1175mm(46")	11,9 mm	1 175,0 mm	22,2 mm
InteGrade profile 2000mm(79")	11,9 mm	2 000,0 mm	22,2 mm
InteGrade profile 875mm(34")	11,9 mm	875,0 mm	22,2 mm



Product	C1	A1	B1	B2
InteGrade profile 2000mm(79") F style	11,9 mm	2 000,0 mm	31,0 mm	26,0 mm

Rozmerový obrázok

Image
not yet
available



Product				
InteGrade magnet for M style profile				


Product	A1	B1	C1	D1
InteGrade engine lock inline	18,7 mm	10 mm	10,7 mm	4,2 mm

Product	A1	B1	C1	D1
InteGrade mounting clip for T style prof	66,5 mm	19,5 mm	5 mm	4,2 mm


Product	A
InteGrade cable 1m(39") white angle	1 000 mm
InteGrade cable 2.5m(98") black angle	2 500 mm
InteGrade cable 2.5m(98") white angle	2 500 mm

Accessories


Rozmerový obrázok



Product	A
InteGrade spacer cable 0.5m white	500 mm



Product	A
InteGrade power cable 1m(39") black	1 000 mm
InteGrade power cable 1m(39") white	1 000 mm
InteGrade power cable 2.5m(98") black	2 500 mm
InteGrade power cable 2.5m(98") white	2 500 mm



Product	C1	A1	B1
InteGrade mounting clip under shelf	12,5 mm	47,0 mm	30,5 mm

