



Continuous slim suspended linear office Luminaire: Performanc and Elegance

Pureline SP680P

The PureLine family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting . The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.

Benefits

- Optimized lighting for office space:smooth and comfortable
- Wider distribution allowing wider row spacing and hence reduction in connected load
- Dimmable and fixed output drivers
- Enhance Interiors

Features

- System efficacy more than 100 Lm/W
- Superior light quality with CRI more than 80
- THD Less than 10%
- Wide operating voltage 140-270V
- Suitable for Standalone & Continuous Mounting
- Option of Dimming available
- Up-Down lighting distribution
- Uniform & volumetric light distribution

Pureline SP680P


Application

- Office Lighting
- Meeting & conference room lighting

Warnings and Safety

- Meant for use in Indoor environment only

Versions




Pureline Suspended8ft-SP680P.JPG

Pureline suspended4ft-SP680P.JPG

Dimensional drawing

Product : Pureline Suspended
Type : SP680
Application : Indoor



Pureline SP680P

General Information	
Driver included	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	100 lm/W
Optic type	-
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220-240 V
Mechanical and Housing	
Optical cover type	Polycarbonate
Housing Color	White
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	0 to +45 °C
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Flux
919515811505	SP680P LED34S 4000 PSU WH L120 S1	4000 K	3,400 lm
919515811506	SP680X1 LED34S 4000 PSU WH L120 S1	4000 K	3,400 lm
919515811507	SP680X2 LED34S 4000 PSU WH L120 S1	4000 K	3,400 lm
919515811521	SP680X1 LED39S 6500 PSD WH L120 S1	6500 K	3,900 lm
919515811526	SP680P LED39S 4000 PSD WH L120 S1	4000 K	3,900 lm
919515811537	SP680X2 LED68S 6500 PSD WH L240 S1	6500 K	6,800 lm
919515811496	SP680P LED39S 6500 PSU WH L120 S1	6500 K	3,900 lm
919515811497	SP680X1 LED39S 6500 PSU WH L120 S1	6500 K	3,900 lm
919515811498	SP680X2 LED39S 6500 PSU WH L120 S1	6500 K	3,900 lm
919515811499	SP680P LED34S 6500 PSU WH L120 S1	6500 K	3,400 lm
919515811501	SP680X2 LED34S 6500 PSU WH L120 S1	6500 K	3,400 lm
919515811502	SP680P LED39S 4000 PSU WH L120 S1	4000 K	3,900 lm
919515811503	SP680X1 LED39S 4000 PSU WH L120 S1	4000 K	3,900 lm
919515811513	SP680X2 LED68S 6500 PSU WH L240 S1	6500 K	6,800 lm
919515811524	SP680X1 LED34S 6500 PSD WH L120 S1	6500 K	3,400 lm
919515811528	SP680X2 LED39S 4000 PSD WH L120 S1	4000 K	3,900 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
919515811505	SP680P LED34S 4000 PSU WH L120 S1	32 W
919515811506	SP680X1 LED34S 4000 PSU WH L120 S1	32 W
919515811507	SP680X2 LED34S 4000 PSU WH L120 S1	32 W
919515811521	SP680X1 LED39S 6500 PSD WH L120 S1	38 W
919515811526	SP680P LED39S 4000 PSD WH L120 S1	38 W
919515811537	SP680X2 LED68S 6500 PSD WH L240 S1	64 W
919515811496	SP680P LED39S 6500 PSU WH L120 S1	38 W
919515811497	SP680X1 LED39S 6500 PSU WH L120 S1	38 W

Order Code	Full Product Name	Power Consumption
919515811498	SP680X2 LED39S 6500 PSU WH L120 S1	38 W
919515811499	SP680P LED34S 6500 PSU WH L120 S1	32 W
919515811501	SP680X2 LED34S 6500 PSU WH L120 S1	32 W
919515811502	SP680P LED39S 4000 PSU WH L120 S1	38 W
919515811503	SP680X1 LED39S 4000 PSU WH L120 S1	38 W
919515811513	SP680X2 LED68S 6500 PSU WH L240 S1	64 W
919515811524	SP680X1 LED34S 6500 PSD WH L120 S1	32 W
919515811528	SP680X2 LED39S 4000 PSD WH L120 S1	38 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
919515811505	SP680P LED34S 4000 PSU WH L120 S1	No
919515811506	SP680X1 LED34S 4000 PSU WH L120 S1	No
919515811507	SP680X2 LED34S 4000 PSU WH L120 S1	No
919515811521	SP680X1 LED39S 6500 PSD WH L120 S1	Yes
919515811526	SP680P LED39S 4000 PSD WH L120 S1	Yes
919515811537	SP680X2 LED68S 6500 PSD WH L240 S1	Yes
919515811496	SP680P LED39S 6500 PSU WH L120 S1	No
919515811497	SP680X1 LED39S 6500 PSU WH L120 S1	No

Order Code	Full Product Name	Dimmable
919515811498	SP680X2 LED39S 6500 PSU WH L120 S1	No
919515811499	SP680P LED34S 6500 PSU WH L120 S1	No
919515811501	SP680X2 LED34S 6500 PSU WH L120 S1	No
919515811502	SP680P LED39S 4000 PSU WH L120 S1	No
919515811503	SP680X1 LED39S 4000 PSU WH L120 S1	No
919515811513	SP680X2 LED68S 6500 PSU WH L240 S1	No
919515811524	SP680X1 LED34S 6500 PSD WH L120 S1	Yes
919515811528	SP680X2 LED39S 4000 PSD WH L120 S1	Yes

