



# Built in light sensor for added security from Dusk-to-Dawn

## LED Dusk to Dawn

Philips Dusk to Dawn A19 lamp is equipped with a built in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises.

### Benefits

- Long life -- lowers maintenance costs by reducing re-lamp frequency
- Excellent color consistency with high 80+ color rendering (CRI)
- Equipped with a built in light sensor that turns your light bulbs on automatically when the sun goes down and turns the light off when the sun rises

### Features

- Fit standard medium base (E26) fixtures with the look and feel of a classic bulb
- Instant on
- 25,000 hour rated average life
- Emits virtually no UV/IR light
- No mercury for a safe environment

### Application

- Security Lighting
- Residential & Assisted Living
- Hotels/Motels

LED Dusk to Dawn

Versions




LEDbulb E27 A19



LEDbulbD2D A19 E27 FR

Dimensional drawing



Product	D	C
LED D2D 60W A60 E27 CW FR ND SRT4	62 mm	114 mm
LED D2D 60W A60 E27 WW FR ND SRT4	62 mm	114 mm

LED Dusk to Dawn

General Information	
Cap-Base	E27
Rated Lifetime (Hours)	15,000 hour(s)
Switching Cycle	50,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Beam Angle (Nom)	250 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux	806 lm
Operating and Electrical	
Input Frequency	50 Hz
Line Frequency	50 Hz
Starting Time (Nom)	0.5 s
Wattage Equivalent	60 W
Temperature	
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A19

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Code
929001383631	LED D2D 60W A60 E27 WW FR ND SRT4	2700 K	827
929001383731	LED D2D 60W A60 E27 CW FR ND SRT4	4000 K	840

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929001383631	LED D2D 60W A60 E27 WW FR ND SRT4	7.5 W

Order Code	Full Product Name	Power Consumption
929001383731	LED D2D 60W A60 E27 CW FR ND SRT4	6.5 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
929001383631	LED D2D 60W A60 E27 WW FR ND SRT4	8 kWh
929001383731	LED D2D 60W A60 E27 CW FR ND SRT4	7 kWh

