



For your everyday lighting jobs, CorePro LED high-lumen bulbs provide excellent quality of light

Corepro Glass High Lumen bulbs

Featuring a classic heritage design, these filament CorePro LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. A very easy choice for people who are looking for a retrofit LED replacement, these high-lumen LED bulbs provide 90% energy savings compared with conventional light bulbs. CorePro LED High Lumen bulbs provide excellent quality of light. Energy-saving LED lighting that offers a lifetime of 15,000 hours to reduce maintenance costs.

Benefits

- Saves 30% energy compared with standard Philips LED bulbs
- Very long lifetime that reduces the need for replacements
- Easy retrofit replacement for conventional lamps

Features

- Heritage design
- High lumen output
- High efficiency
- Long lifetime
- Easy installation

Corepro Glass High Lumen bulbs


Application

- Home
- Warehouses

Versions





LEDclassic A95 E27 FR-POS2A



LEDclassic A67 E27 CL 1-POS2A

Dimensional drawing



Product	D	C
CorePro LEDBulbND17-150W E27 A67 827 CLG	70 mm	128 mm

Product	D	C
CorePro LEDBulbND 200W E27 A95 865 FR G	95 mm	165 mm

Corepro Glass High Lumen bulbs

General Information	
Cap base	E27
Switching Cycle	20,000
Nominal lifetime	15,000 h
Light Technical	
Beam angle (nom.)	300 degree(s)
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting time (nom.)	0.5 s
Controls and Dimming	
Dimmable	No

Light Technical

Order Code	Full Product Name	Correlated Colour	Colour	Luminous Flux
		Temperature (Nom)	Code	
34671000	CorePro LEDBulbND 200W E27 A95 865 FR G	6500 K	865	3,452 lm
34744100	CorePro LEDBulbND17-150W E27 A67 827 CLG	2700 K	827	2,452 lm

Operating and Electrical

Order Code	Full Product Name	Power	Wattage
		Consumption	equivalent
34671000	CorePro LEDBulbND 200W E27 A95 865 FR G	23 W	200 W

Order Code	Full Product Name	Power	Wattage
		Consumption	equivalent
34744100	CorePro LEDBulbND17-150W E27 A67 827 CLG	17 W	150 W

Temperature

Order Code	Full Product Name	T-Case maximum (nom.)
34671000	CorePro LEDBulbND 200W E27 A95 865 FR G	55 °C

Order Code	Full Product Name	T-Case maximum (nom.)
34744100	CorePro LEDBulbND17-150W E27 A67 827 CLG	60 °C



Mechanical and Housing

Order Code	Full Product Name	Lamp Finish	Bulb shape
34671000	CorePro LEDBulbND 200W E27 A95 865 FR G	Frosted	A95

Order Code	Full Product Name	Lamp Finish	Bulb shape
34744100	CorePro LEDBulbND17-150W E27 A67 827 CLG	Clear	A67

Approval and Application

Order Code	Full Product Name	Energy consumption kWh/
		1,000 hours
34671000	CorePro LEDBulbND 200W E27 A95 865 FR G	23 kWh
34744100	CorePro LEDBulbND17-150W E27 A67 827 CLG	17 kWh



Corepro Glass High Lumen bulbs

