



LED lamps for the special applications

CorePro Plastic LED Specialties

The LED specialties can be easily installed for certain applications.

Benefits

- energy saving with LED technology
- easy choice and installation

Features

- energy saving with LED technology
- Long lifetime
- easy installation

Application

- Home
- Hotel
- Retail

Versions





LEDbulb CorePro 9.5-68W E27
Stick Frost 830 24D ND



LED T25 E14 WW C1 POS1

CorePro Plastic LED Specialties

Dimensional drawing



Product	D	C
Corepro LED T25 ND 1.7-15W E14 827	25 mm	59 mm

Product	D	C
CorePro LED Stick ND 9.5-68W T38 E27 830	37.2 mm	114.3 mm
CorePro LED Stick ND 9.5-75W T38 E27 840	37.2 mm	114.3 mm

General Information	
Switching Cycle	50,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Beam Angle (Nom)	240 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted

General Information

Order Code	Full Product Name	Cap-Base
929001901402	CorePro LED Stick ND 9.5-68W T38 E27 830	E27
929001901502	CorePro LED Stick ND 9.5-75W T38 E27 840	E27
929001325702	Corepro LED T25 ND 1.7-15W E14 827	E14

Light Technical

CorePro Plastic LED Specialties

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929001901402	CorePro LED Stick ND 9.5-68W T38 E27 830	3000 K	830	950 lm
929001901502	CorePro LED Stick ND 9.5-75W T38 E27 840	4000 K	840	1,050 lm

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929001325702	Corepro LED T25 ND 1.7-15W E14 827	2700 K	827	150 lm

Operating and Electrical

Order Code	Full Product Name	Power	Wattage
		Consumption	Equivalent
929001901402	CorePro LED Stick ND 9.5-68W T38 E27 830	9.5 W	68 W
929001901502	CorePro LED Stick ND 9.5-75W T38 E27 840	9.5 W	75 W

Order Code	Full Product Name	Power	Wattage
		Consumption	Equivalent
929001325702	Corepro LED T25 ND 1.7-15W E14 827	1.7 W	15 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001901402	CorePro LED Stick ND 9.5-68W T38 E27 830	85 °C
929001901502	CorePro LED Stick ND 9.5-75W T38 E27 840	85 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001325702	Corepro LED T25 ND 1.7-15W E14 827	55 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929001901402	CorePro LED Stick ND 9.5-68W T38 E27 830	Stick
929001901502	CorePro LED Stick ND 9.5-75W T38 E27 840	Stick

Order Code	Full Product Name	Bulb Shape
929001325702	Corepro LED T25 ND 1.7-15W E14 827	T25

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
929001901402	CorePro LED Stick ND 9.5-68W T38 E27 830	10 kWh
929001901502	CorePro LED Stick ND 9.5-75W T38 E27 840	10 kWh
929001325702	Corepro LED T25 ND 1.7-15W E14 827	2 kWh

