



One choice, five colors

Essential SmartBright LED bulb.

Not sure about the color that will best fit your application? No need to worry. Philips Dipswitch LED bulb offer 5 colors in one product and is easy-to-operate by switching the button to change the color.

Benefits

- Enjoy 5 possible light colors in one product
- Change the color of your light easily with by switching the button on the product
- No guesswork

Features

- 5 color temperatures
- Dimmable
- Change the color by switching the button
- Lifetime up to 15,000 hours
- Easy retrofit

Application

- Home
- Offices
- Education

Essential SmartBright LED bulb.

Versions



LEDBulb 9W B22 DS FR DIM 1PF 6
AU RTP



LEDStick 14W E27 DS FR DIM 1PF
6 AU RTP



LEDBulb 14W E27 DS FR DIM 1PF 6
AU RTP



LEDStick 10W B22 DS FR DIM 1PF
6 AU RTP



LEDBulb 14W B22 DS FR DIM 1PF 6
AU RTP



LEDBulb 9W E27 DS FR DIM 1PF 6
AU RTP







LEDStick 10W E27 DS FR DIM 1PF
6 AU RTP



LEDStick 14W B22 DS FR DIM 1PF
6 AU RTP

Essential SmartBright LED bulb.

Dimensional drawing



Product	D	C
LEDBulb 14W E27 DS FR DIM 1PF/6 AU	60 mm	119 mm
LEDBulb 9W E27 DS FR DIM 1PF/6 AU	60 mm	115 mm



Product	D	C
LEDStick 10W B22 DS FR DIM 1PF/6 AU	41 mm	106 mm

Product	D	C
LEDStick 14W E27 DS FR DIM 1PF/6 AU	41 mm	133 mm

Product	D	C
LEDStick 14W B22 DS FR DIM 1PF/6 AU	41 mm	132 mm

Essential SmartBright LED bulb.

Dimensional drawing



Product	D	C
LEDBulb 14W B22 DS FR DIM 1PF/6 AU	60 mm	118 mm
LEDBulb 9W B22 DS FR DIM 1PF/6 AU	60 mm	114 mm

Product	D	C
LEDStick 10W E27 DS FR DIM 1PF/6 AU	41 mm	107 mm

Essential SmartBright LED bulb.

General Information	
Switching Cycle	50,000
Nominal lifetime	15,000 h
Light Technical	
Beam Angle (Nom)	200 degree(s)
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	80
Color Code	2700K/3000K/ 4000K/5000K/ 6500K
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Approval and Application	
Ambient temperature range	-20 to +45 °C

General Information

Order Code	Full Product Name	Cap-Base
929003785319	LEDBulb 9W B22 DS FR DIM 1PF/6 AU	B22
929003785819	LEDStick 14W E27 DS FR DIM 1PF/6 AU	E27
929003785419	LEDBulb 14W E27 DS FR DIM 1PF/6 AU	E27
929003785719	LEDStick 10W B22 DS FR DIM 1PF/6 AU	B22
929003785519	LEDBulb 14W B22 DS FR DIM 1PF/6 AU	B22
929003785219	LEDBulb 9W E27 DS FR DIM 1PF/6 AU	E27
929003785619	LEDStick 10W E27 DS FR DIM 1PF/6 AU	E27
929003785919	LEDStick 14W B22 DS FR DIM 1PF/6 AU	B22

Light Technical

Order Code	Full Product Name	Luminous Flux
929003785319	LEDBulb 9W B22 DS FR DIM 1PF/6 AU	900 lm
929003785819	LEDStick 14W E27 DS FR DIM 1PF/6 AU	1,400 lm
929003785419	LEDBulb 14W E27 DS FR DIM 1PF/6 AU	1,400 lm
929003785719	LEDStick 10W B22 DS FR DIM 1PF/6 AU	1,000 lm

Order Code	Full Product Name	Luminous Flux
929003785519	LEDBulb 14W B22 DS FR DIM 1PF/6 AU	1,400 lm
929003785219	LEDBulb 9W E27 DS FR DIM 1PF/6 AU	900 lm
929003785619	LEDStick 10W E27 DS FR DIM 1PF/6 AU	1,000 lm
929003785919	LEDStick 14W B22 DS FR DIM 1PF/6 AU	1,400 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003785319	LEDBulb 9W B22 DS FR DIM 1PF/6 AU	9 W	60 W
929003785819	LEDStick 14W E27 DS FR DIM 1PF/6 AU	14 W	100 W
929003785419	LEDBulb 14W E27 DS FR DIM 1PF/6 AU	14 W	100 W
929003785719	LEDStick 10W B22 DS FR DIM 1PF/6 AU	10 W	75 W

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003785519	LEDBulb 14W B22 DS FR DIM 1PF/6 AU	14 W	100 W
929003785219	LEDBulb 9W E27 DS FR DIM 1PF/6 AU	9 W	60 W
929003785619	LEDStick 10W E27 DS FR DIM 1PF/6 AU	10 W	75 W
929003785919	LEDStick 14W B22 DS FR DIM 1PF/6 AU	14 W	100 W

Mechanical and Housing

Essential SmartBright LED bulb.

Order Code	Full Product Name	Bulb Shape
929003785319	LED Bulb 9W B22 DS FR DIM 1PF/6 AU	A60
929003785819	LED Stick 14W E27 DS FR DIM 1PF/6 AU	Stick
929003785419	LED Bulb 14W E27 DS FR DIM 1PF/6 AU	A60
929003785719	LED Stick 10W B22 DS FR DIM 1PF/6 AU	Stick
929003785519	LED Bulb 14W B22 DS FR DIM 1PF/6 AU	A60
929003785219	LED Bulb 9W E27 DS FR DIM 1PF/6 AU	A60
929003785619	LED Stick 10W E27 DS FR DIM 1PF/6 AU	Stick
929003785919	LED Stick 14W B22 DS FR DIM 1PF/6 AU	Stick

