



# The new generation of energy-saving LED PLT 4P tube lighting

## CorePro LED PLT 4P

The CorePro LED PLT 4P integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplampping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly

### Benefits

- Highly energy-efficient
- Easy installation
- Conventional form factor to fit into existing luminaire
- No mercury

### Features

- Reduced operational cost thanks to lower energy consumption
- Lower maintenance cost thanks to 2-3 times longer lifetime than conventional lamps
- Fastest and easiest way to upgrade existing luminaires to LED technology
- Completely safe product and installation process

### Application

- Hospitality, retail, office, industrial and home applications

# CorePro LED PLT 4P


## Versions




LEDtube COR PLT 15W GX24Q3

LEDtube COR PLT 18.5W GX24Q4

## Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LED PLT HF 15W 830 4P GX24q-3	42 mm	42 mm	129 mm	141 mm	156 mm



Product	D1	D2	A1	A2	A3
CorePro LED PLT HF 18.5W 840 4P GX24q-4	42 mm	42 mm	139 mm	151 mm	166 mm

CorePro LED PLT 4P

General Information	
Switching Cycle	200,000
Nominal lifetime	30,000 hour(s)
Light Technical	
Beam Angle (Nom)	120 degree(s)
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	20K-80K Hz
Line Frequency	20K-80K Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	PL-T
Approval and Application	
Ambient temperature range	-20 °C to 35 °C

General Information

Order Code	Full Product Name	Cap-Base
929003576702	CorePro LED PLT HF 15W 830 4P GX24q-3	GX24q-3
929003577002	CorePro LED PLT HF 18.5W 840 4P GX24q-4	GX24q-4

Light Technical

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929003576702	CorePro LED PLT HF 15W 830 4P GX24q-3	3000 K	830	1,620 lm

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929003577002	CorePro LED PLT HF 18.5W 840 4P GX24q-4	4000 K	840	2,250 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929003576702	CorePro LED PLT HF 15W 830 4P GX24q-3	15 W

Order Code	Full Product Name	Power Consumption
929003577002	CorePro LED PLT HF 18.5W 840 4P GX24q-4	18.5 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003576702	CorePro LED PLT HF 15W 830 4P GX24q-3	70 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003577002	CorePro LED PLT HF 18.5W 840 4P GX24q-4	75 °C

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003576702	CorePro LED PLT HF 15W 830 4P GX24q-3	15 kWh
929003577002	CorePro LED PLT HF 18.5W 840 4P GX24q-4	19 kWh

CorePro LED PLT 4P

