



Metronomis LED: a play of light and shadow

Metronomis LED Sharp

Metronomis LED is the first post-top luminaire range in the world to offer a palette of lighting effects to give projects a unique contextual or aesthetic touch. An innovative play of reflection, light and shadow that casts a pattern on the ground or in the bowl, to create additional ambience. Four iconic designs are available: Metronomis LED Torch (BDS650), Metronomis LED Torch with hat (BDS651), Metronomis LED Sharp (BDS660) and Metronomis LED Fluid (BDS670). Each luminaire design has a visual and modular link to Metronomis I, reduced to its essential elements. During the day, the discreet, transparent design blends into its urban context, whether that be contemporary or classical architecture and surroundings, while its night-time appearance is both functional and decorative. Flexible and modular, the Metronomis LED family comes with a range of columns and a wide variety of effects. This enables architects and lighting designers to create a unified, consistent lighting design across any cityscape, while still reflecting the differences in urban culture and history. Metronomis LED also offers all the benefits of LEDGINE. Energy saving, serviceable and upgradable, this luminaire range is designed to maintain excellent light quality over its lifetime.

Benefits

- Create a unique city identity with a pure design and palette of lighting effects
- A complete and innovative solution with a shared design identity for mast and luminaires
- Exceptional visual comfort with multiple geometries to optimise safety
- Future-ready with a Zhaga-D4i system ready (SR) top socket to connect with Interact controls
- Service tag for easy installation and maintenance

Metronomis LED Sharp

Features

- Large choice of light effects (on ground, inside/outside bowl)
- 2D engraving option to personalise luminaires further
- Choice of colour temperatures and colour rendering for different ambiances: 2,200 K, 2,700 K, 3,000 K and 4,000 K
- Efficacy up to 157 lm/W
- Torch version with ULR <1%
- Lifetime up to 100,000 hours @L96 B10
- Five dedicated aluminium and wooden masts (3.5 and 4 metres)
- 5-year standard warranty (option to extend up to 10 years)

Application


- City centers and squares
- Commercial and business centers
- Residential and architectural areas
- Cycle paths, footpaths

Versions



OPPR BDS650i 0013

Dimensional drawing



Metronomis LED Sharp

Product details



OPDP_BDS650i_0001-Detail photo



OPDP_BDS650i_0003-Detail photo



OPDP_BDS650i_0023-Detail photo



OPDP_BDS650i_0025-Detail photo



OPDP_BDS650i_0027-Detail photo



OPDP_BDS650i_0029-Detail photo



OPDP_BDS650i_0031-Detail photo



OPDP_BDS650i_0033-Detail photo

Metronomis LED Sharp

Product details



OPDP_BDS650i_0035-Detail
photo



OPDP_BDS650i_0037-Detail
photo




OPDP_BDS650i_0039-Detail
photo




OPDP_BDS650i_0041-Detail
photo




OPDP_BDS650i_0045-Detail
photo



OPDP_BDS650i_0047-Detail
photo



OPDP_BDS650i_0049-Detail
photo



OPDP_BDS650i_0051-Detail
photo

Metronomis LED Sharp

Product details




OPDP_BDS650i_0053-Detail
photo



OPDP_BDS650i_0055-Detail
photo

Polar Wide Diagrams



Polar Normal (separate) - BDS650I -
910925868165

