



Feel more safe

FWC LED

Only texts for Benelux market available

Benefits

- Only texts for Benelux market available

Features

- Only texts for Benelux market available

Application


- Only texts for Benelux market available

Versions



OPPR BWC110i 0007

Dimensional drawing



General Information

Driver included	Yes
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes

Light Technical

Luminaire light beam spread	180°
Light source color	830 warm white
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	80
Number of light sources	1
Optic type outdoor	Symmetrical
Upward light output ratio	0.08

Operating and Electrical

Surge Protection (Common/ Differential)	Standard surge protection level
--	------------------------------------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Optical cover type	Opal bowl/cover
Mech. impact protection code	IK08
Ingress protection code	IP54
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°

Approval and Application

CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1 %
-------------------------------	-----

General Information

Order Code	Full Product Name	Lamp family code
85195099	BWC120 LED18-/830 PSU II BK	LED18
85190599	BWC110 LED9-/830 PSU II WH PH	LED9
85194399	BWC120 LED18-/830 PSU II WH PH	LED18

Light Technical

Order Code	Full Product Name	Luminous Flux
85195099	BWC120 LED18-/830 PSU II BK	1,800 lm
85190599	BWC110 LED9-/830 PSU II WH PH	900 lm

Order Code	Full Product Name	Luminous Flux
85194399	BWC120 LED18-/830 PSU II WH PH	1,800 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
85195099	BWC120 LED18-/830 PSU II BK	16 W
85190599	BWC110 LED9-/830 PSU II WH PH	9 W

Order Code	Full Product Name	Power Consumption
85194399	BWC120 LED18-/830 PSU II WH PH	16 W

Mechanical and Housing

Order Code	Full Product Name	Housing Color
85195099	BWC120 LED18-/830 PSU II BK	Black
85190599	BWC110 LED9-/830 PSU II WH PH	White

Order Code	Full Product Name	Housing Color
85194399	BWC120 LED18-/830 PSU II WH PH	White

Product Data

Order Code	Full Product Name	Product family code
85195099	BWC120 LED18-/830 PSU II BK	BWC120
85190599	BWC110 LED9-/830 PSU II WH PH	BWC110

Order Code	Full Product Name	Product family code
85194399	BWC120 LED18-/830 PSU II WH PH	BWC120

