



# Product Description

## MASTER PL-C 4 Pin

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

### Benefits

- Optimal light performance for short or long operation per switch on
- Long life and sustainable light output

### Features

- 4-pin base without starter and capacitor
- Lamp characteristics are influenced by operating conditions and control gear used
- Dimming is possible

### Application

- Designed for general or supplementary lighting in professional or home environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

# MASTER PL-C 4 Pin

## Versions




LPPR PLC4P 18W



LPPR PLC4P 26W

## Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 18W/865/4P 1CT/5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm
MASTER PL-C 26W/865/4P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm

Light Technical	
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	80
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg

## General Information

Order Code	Full Product Name	Cap-Base
927907286501	MASTER PL-C 18W/865/4P 1CT/5X10BOX	G24q-2

Order Code	Full Product Name	Cap-Base
927907386565	MASTER PL-C 26W/865/4P 1CT/5X10BOX	G24q-3

## Light Technical

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
927907286501	MASTER PL-C 18W/865/4P 1CT/5X10BOX	62.3 lm/W	1,120 lm

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
927907386565	MASTER PL-C 26W/865/4P 1CT/5X10BOX	66 lm/W	1,740 lm

# MASTER PL-C 4 Pin

## Operating and Electrical

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
927907286501	MASTER PL-C 18W/865/4P 1CT/5X10BOX	0.230 A	18.0 W

Order Code	Full Product Name	Lamp Current	Power Consumption
		(Nom)	
927907386565	MASTER PL-C 26W/865/4P 1CT/5X10BOX	0.335 A	26.0 W

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927907286501	MASTER PL-C 18W/865/4P 1CT/ 5X10BOX	20 kWh

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
927907386565	MASTER PL-C 26W/865/4P 1CT/ 5X10BOX	29 kWh

