



Philips EcoSet 基本控制系统 — 以简单、可靠且经济实惠的方式节约能源

EcoSet 基本控制

使用 Philips EcoSet 基本控制系统将您的照明解决方案节能水平提升到全新高度。该传感器解决方案匠心打造，提供简单、可靠且经济实惠的节能效果，同时进一步增强能源可持续性。从办公室照明、停车场照明到工业照明应用，Philips EcoSet 基本控制系统根据您的具体需求提供不同版本，无论是即插即用还是有线或无线版本，一应俱全。该系统的工作原理是使用基本控制解决方案的所有功能对传统灯具或 LED 灯具进行升级。因此，您可以尽享运动检测、日光采集或组照明控制等节能优势。此外，Philips EcoSet 基本控制传感器易于安装、调试和维护，因此您能够完全控制现有照明解决方案的能耗，获得可靠且经济实惠的节能效果。

优点

- 简单的系统架构，提供多种选择 — 有线或无线；带有集成传感器或外部传感器
- 专为节能而设计
- 借助即插即用选项，轻松创建网络
- 轻松调试

特点

- 运动和日光检测
- 自动调光功能和分组控制
- 解决方案包括：一键式调试版、无线免调试选项、通过遥控器简单调试。
- 一个网络中有多达 50 个节点，适合无线办公室或仓库。

应用

- 所有室内应用

Versions



EcoSet parking office wireless sensor std photo



EcoSet BLE IR Remote Controller std photo



EcoSet BLE Switch Dim installation std photo

操作和电气

Order Code	Full Product Name	频率	频率	Order Code	Full Product Name	频率	频率
911401542902	SEG101 PIR Wireless WH	-	-	911401590622	EcoSet BLE IR Remote Controller	- Hz	- Hz
911401543002	SEG101 PIR IP65 Wireless WH	-	-	911401590722	EcoSet BLE Switch Dim	-	-

温度

Order Code	Full Product Name	环境温度范围	Order Code	Full Product Name	环境温度范围
911401542902	SEG101 PIR Wireless WH	-20 至 +50°C	911401590622	EcoSet BLE IR Remote Controller	-5 至 +40°C
911401543002	SEG101 PIR IP65 Wireless WH	-20 至 +50°C	911401590722	EcoSet BLE Switch Dim	0 至 +45°C

审批和申请

Order Code	Full Product Name	CE 标志	CE 标志	Order Code	Full Product Name	CE 标志	CE 标志
911401542902	SEG101 PIR Wireless WH	CE 标志	CE 标志	911401543002	SEG101 PIR IP65 Wireless WH	CE 标志	CE 标志

