



Retail Sales T12

Retail Sales T12

High Performance, Long Life, Environmentally-Responsible Lamps. These high performance lamps are ideal for applications where high lumens, long life and high CRI are required.

Versions



75W T12 Daylight Deluxe Tubular
Fluorescent - RFT



LPPR F-T12-RS G13 GB



15W T12 Soft White Tubular
Fluorescent - RFT

Retail Sales T12

Versions




14W T12 Soft White Tubular
Fluorescent - RFT




40W T12 Daylight Deluxe Tubular
Fluorescent - RFT

Dimensional drawing




Product

75W T12 Daylight Deluxe Tubular Fluorescent



Product

- 14W T12 Soft White Tubular Fluorescent
- 15W T12 Soft White Tubular Fluorescent



Product

- 40W T12 Daylight Deluxe Tubular Fluorescent
- F40T12/DAYLIGHT DELUXE/ALTO 30PK

Retail Sales T12

Mechanical and Housing	
Bulb Shape	T-12

General Information

Order Code	Full Product Name	Cap-Base
927895005722	75W T12 Daylight Deluxe Tubular Fluorescent	FA8
927888005733	F40T12/DAYLIGHT DELUXE/ALTO 30PK	G13
927882083004	15W T12 Soft White Tubular Fluorescent	G13

Order Code	Full Product Name	Cap-Base
927881083003	14W T12 Soft White Tubular Fluorescent	G13
927888005728	40W T12 Daylight Deluxe Tubular Fluorescent	G13

Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
927895005722	75W T12 Daylight Deluxe Tubular Fluorescent	Daylight	6500 K	90	4,775 lm
927888005733	F40T12/DAYLIGHT DELUXE/ALTO 30PK	Daylight	6500 K	90	2,325 lm
927882083004	15W T12 Soft White Tubular Fluorescent	Ultralume 30	3000 K	85	800 lm

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
927881083003	14W T12 Soft White Tubular Fluorescent	Ultralume 30	3000 K	85	700 lm
927888005728	40W T12 Daylight Deluxe Tubular Fluorescent	Daylight	6500 K	90	2,325 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
927895005722	75W T12 Daylight Deluxe Tubular Fluorescent	75 W
927888005733	F40T12/DAYLIGHT DELUXE/ALTO 30PK	40 W
927882083004	15W T12 Soft White Tubular Fluorescent	15 W

Order Code	Full Product Name	Power Consumption
927881083003	14W T12 Soft White Tubular Fluorescent	14 W
927888005728	40W T12 Daylight Deluxe Tubular Fluorescent	40 W

Approval and Application

Order Code	Full Product Name	Energy Saving Product	Mercury (Hg) Content (Nom)
927895005722	75W T12 Daylight Deluxe Tubular Fluorescent	Not Applicable	6.8 mg
927888005733	F40T12/DAYLIGHT DELUXE/ALTO 30PK	Not Applicable	4.4 mg
927882083004	15W T12 Soft White Tubular Fluorescent	-	-

Order Code	Full Product Name	Energy Saving Product	Mercury (Hg) Content (Nom)
927881083003	14W T12 Soft White Tubular Fluorescent	-	-
927888005728	40W T12 Daylight Deluxe Tubular Fluorescent	Not Applicable	4.4 mg

