Trusted quality for best performance

Essential LV MR16

The Essential LV MR16 is part of the Philips "Value for Money" ranges. It is a good choice for professional end-users looking for high-quality accent light to create contrast in shops, hotels and restaurants.

Avantages

- Accent light to create the perfect focus on the objects to be lit
- Cool beam to minimize the effects of halogen light on sensitive objects
- Best dimmability to meet different brightness requirements

Fonctions

- Bright sparkling light to create ambient atmosphere.
- Excellent color rendering (Ra=100) to present the true color of objects.
- Instant start to offer direct brightness from the moment switch on.
- No mercury to ensure the safety usage.
- Reliable quality to be trusted.

Application

- Shops, hotels and restaurants

Les données sont sujettes à changement

Essential LV MR16

Schéma dimensionnel



Product	D (max)	C (max)
20 W GU5.3 cap Warm white Halogen spot	51 mm	46 mm
50 W GU5.3 cap Warm white Halogen spot	51 mm	46 mm

Informations générales

Culot	GU5.3
Durée de vie nominale (heures)	2 000 h
Cycle d'allumage	8 000
Durée de vie nominale	2 000 h
Position de fonctionnement	UNIVERSEL

Données techniques de l'éclairage

Angle d'émission du faisceau (nom.)	36 degré(s)
Température de couleur corrélée (nom.)	3000 K
Indice de rendu de couleur (IRC)	100

Fonctionnement et électricité

Tension (nom.)	12 V
Heure de démarrage (nom.)	0,0 s

Commandes et gradation

Variation de l'intensité lumineuse	Oui

Mécanique et boîtier

Forme de l'ampoule	MR16

Fonctionnement et électricité

Order Code	Full Product Name	Courant lampe (nom.)	Consommation électrique
924049517186	20 W GU5.3 cap Warm white Halogen spot	1,67 A	20 W
926000850012	50 W GU5.3 cap Warm white Halogen spot	4,17 A	50 W

Approbation et application

Order Code	Full Product Name	Consommation d'énergie kWh/1 000 h
924049517186	20 W GU5.3 cap Warm white Halogen spot	-

Order Code	Full Product Name	Consommation d'énergie kWh/1 000 h
926000850012	50 W GU5.3 cap Warm white Halogen spot	53 kWh

Essential LV MR16

© 2024 Signify Holding Tous droits réservés. Signify ne fait aucune déclaration ni ne donne aucune garantie concernant la précision ou l'exhaustivité des informations ci-incluses et ne pourra être tenue responsable d'une quelconque action prise en conséquence. Les informations présentées dans ce document ne constituent pas une offre commerciale et ne font partie d'aucun devis ni d'aucun contrat, sauf convention contraire avec Signify. Toutes les marques commerciales sont la propriété de Signify Holding ou de leurs propriétaires respectifs.

www.lighting.philips.com
2024, juillet 5 - Les données sont sujettes à changement