



Product Description

Plusline Compact

Mains-voltage linear lamp giving white halogen light

Benefits

- Bright halogen light
- Long lifetime

Features

- Clear tubular quartz bulb
- Reinforced filament supports for maximum safety and shock resistance resulting in longer lifetime
- Two arc-preventing fuses for greater safety
- Excellent colour rendering
- Constant light output during life

Application

- Typically used in shop lighting applications
- Indoor: homes, offices, shops and museums
- Outdoor: billboards, car parks, security lighting and construction sites

Plusline Compact

Versions




8711500885388 - RFT



LPPR HDECOMP R7s 10

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
100 W R7s cap Clear Halogen linear lamp	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm
150 W R7s cap Clear Halogen linear lamp	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm
Plusline C 100W R7s 230V 1CT/10X10F	12 mm	76.5 mm	74.9 mm	73.3 mm	78 mm
Plusline C 150W R7s 240V 1BC/12	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm

General Information	
Cap-Base	R7s
Rated Lifetime (Hours)	2,000 hour(s)
Nominal lifetime	2,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3

Light Technical				
Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
923919943202	150 W R7s cap Clear Halogen linear lamp	-	16 lm/W	2,400 lm
923920045792	100 W R7s cap Clear Halogen linear lamp	-	15.5 lm/W	1,550 lm
923919945709	Plusline C 150W R7s 240V 1BC/12	-	16 lm/W	2,400 lm
923920043290	Plusline C 100W R7s 230V 1CT/10X10F	2800 K	15.5 lm/W	1,550 lm

Operating and Electrical

Plusline Compact

Order Code	Full Product Name	Lamp	Voltage (Nom)	Power Consumption
		Current (Nom)		
923919943202	150 W R7s cap Clear Halogen linear lamp	0.65 A	230 V	150 W
923920045792	100 W R7s cap Clear Halogen linear lamp	0.42 A	240 V	100 W

Order Code	Full Product Name	Lamp	Voltage (Nom)	Power Consumption
		Current (Nom)		
923919945709	Plusline C 150W R7s 240V 1BC/12	0.63 A	240 V	150 W
923920043290	Plusline C 100W R7s 230V 1CT/10X10F	0.43 A	230 V	100 W

