



Product Description

Plusline Large

Mains-voltage linear lamp giving white halogen light

Benefits

- Bright halogen light
- Long lifetime of 2000 hours


Features

- Clear tubular quartz bulb
- Constant light output during life
- Colour temperature 2900K
- Excellent colour rendering (R_a = 100)
- Limited burning position: +/-4°

Application

- Typically used in outdoor applications: billboards, car parks, security lighting and construction sites
- Also used in Indoor applications: homes, offices, shops and museums

Versions



8727900808551 - RFT





LPPR_HDEBIG_R7s-Product photo



LPPR HLINEAR 0001

Plusline Large

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
1000 W R7s cap Clear Halogen linear lamp	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm
1000 W R7s cap Clear Halogen linear lamp	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm
1500 W R7s cap Clear Halogen linear lamp	11 mm	252.3 mm	250.7 mm	249.1 mm	254.1 mm
Plusline L 1000W R7s 230V 1CT/10	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm

Product	D (max)	C (max)
Plusline L 500W 240-250V CL 1SL/4X50CT	12.75 mm	185.7 mm

General Information	
Cap-Base	R7s
Rated Lifetime (Hours)	2,000 hour(s)
Mechanical and Housing	
Bulb Finish	Clear

General Information

Order Code	Full Product Name	Switching Cycle	Nominal lifetime	Operating Position
923932145741	1000 W R7s cap Clear Halogen linear lamp	8,000	2,000 hour(s)	P4
923932143241	1000 W R7s cap Clear Halogen linear lamp	8,000	2,000 hour(s)	P4
923932243241	1500 W R7s cap Clear Halogen linear lamp	8,000	2,000 hour(s)	P4

Order Code	Full Product Name	Switching Cycle	Nominal lifetime	Operating Position
923932143293	Plusline L 1000W R7s 230V 1CT/10	8,000	2,000 hour(s)	P4
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	-	-	UNIVERSAL

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
923932145741	1000 W R7s cap Clear	2900 K	100	21.5 lm/W	21,500 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	Halogen linear lamp				

Plusline Large

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
923932143241	1000 W R7s cap Clear Halogen linear lamp	2900 K	100	21.5 lm/W	21,500 lm
923932243241	1500 W R7s cap Clear Halogen linear lamp	2900 K	100	22 lm/W	33,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
923932143293	Plusline L 1000W R7s 230V 1CT/10	2900 K	100	21.5 lm/W	21,500 lm
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	-	-	-	8,900 lm

Operating and Electrical

Order Code	Full Product Name	Warm-up time to 60% light	Lamp Current (Nom)	Voltage (Nom)	Power Consumption	Starting Time (Nom)
923932145741	1000 W R7s cap Clear Halogen linear lamp	instant full light s	4.17 A	240 V	1,000.0 W	0.0 s
923932143241	1000 W R7s cap Clear Halogen linear lamp	instant full light s	4.35 A	230 V	1,000 W	0.0 s
923932243241	1500 W R7s cap Clear Halogen linear lamp	instant full light s	6.52 A	230 V	1,500.0 W	0.0 s
923932143293	Plusline L 1000W R7s 230V 1CT/10	instant full light s	4.35 A	230 V	1,000 W	0.0 s
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	-	-	240-250 V	500 W	-

Controls and Dimming

Order Code	Full Product Name	Dimmable
923932145741	1000 W R7s cap Clear Halogen linear lamp	Yes
923932143241	1000 W R7s cap Clear Halogen linear lamp	Yes
923932243241	1500 W R7s cap Clear Halogen linear lamp	Yes

Order Code	Full Product Name	Dimmable
923932143293	Plusline L 1000W R7s 230V 1CT/10	Yes
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	-

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
923932145741	1000 W R7s cap Clear Halogen linear lamp	T11
923932143241	1000 W R7s cap Clear Halogen linear lamp	T11
923932243241	1500 W R7s cap Clear Halogen linear lamp	T11

Order Code	Full Product Name	Bulb Shape
923932143293	Plusline L 1000W R7s 230V 1CT/10	T11
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	T37

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
923932145741	1000 W R7s cap Clear Halogen linear lamp	1,000 kWh
923932143241	1000 W R7s cap Clear Halogen linear lamp	1,000 kWh
923932243241	1500 W R7s cap Clear Halogen linear lamp	1,500 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
923932143293	Plusline L 1000W R7s 230V 1CT/10	1,000 kWh
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	-

