



# Double Ended Linear

## Double Ended Linear

High-quality white light with superior lumen performance. Halogen Double Ended lamps provide bright, white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs. High lumen output provides light where you need it.

### Benefits

- Provides high lumen output.
- Available in several lengths to meet specific applications.

### Features

- Bright, white light.
- Available in wide range of wattages.
- Recessed Single Contact (RSC).
- Available in 100, 150, 250, 300, and 500 watts.

### Application

- Ideal for work lights, torchieres, sconces, outdoor security fixtures.

### Versions



LPPR\_HDESMALL\_R7s-Product  
photo



500 W RSC base Clear Linear -  
RFT


# Double Ended Linear

## Versions



300W RSC Sparkling light Work  
and Security Light - RFT

## Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
300W RSC Sparkling light Work and Security Light	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
500 W RSC base Clear Dimmable Linear	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
PLUS PRO S 500W R7s 120V 1CT/12	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

General Information	
Cap-Base	R7s
Rated Lifetime (Hours)	2,000 hour(s)
Nominal lifetime	2,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	2900 K
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	120 V
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3

Order Code	Full Product Name	Operating Position
924735334593	PLUS PRO S 500W R7s 120V 1CT/12	UNIVERSAL
924735334596	500 W RSC base Clear Dimmable Linear	UNIVERSAL
924884936301	300W RSC Sparkling light Work and Security Light	P4

## Light Technical

Double Ended Linear

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
924735334593	PLUS PRO S 500W R7s 120V 1CT/12	19.0 lm/W	9,500 lm
924735334596	500 W RSC base Clear Dimmable Linear	19.0 lm/W	9,500 lm

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
924884936301	300W RSC Sparkling light Work and Security Light	16 lm/W	5,000 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current	Power
		(Nom)	Consumption
924735334593	PLUS PRO S 500W R7s 120V 1CT/12	4.17 A	500 W
924735334596	500 W RSC base Clear Dimmable Linear	4.17 A	500 W

Order Code	Full Product Name	Lamp Current	Power
		(Nom)	Consumption
924884936301	300W RSC Sparkling light Work and Security Light	2.5 A	300 W

