



Product Description

CLASSICTONE Standard

Conventional pear-shaped incandescent lamps

Benefits

- Brilliant, visible filament adds friendly points of brightness for an enriched lighting effect


Features

- Vacuum-filled (15W) or gas-filled (25W and above)
- Choice of clear or frosted lamp types
- Universal burning position

Application

- Clear lamps are ideal for indirect lighting in closed luminaires, and where brilliance and sparkling effects are more important than reduction of glare
- Frosted lamps give low glare and diffused lighting for universal applicability

Dimensional drawing



| Product | D (max) | D | C (max) |
|---|---------|-------|---------|
| CLAS 15W E27 220-240V A55 CL 1CT/10X10F | 56 mm | 55 mm | 97 mm |
| CLAS 25W E27 220-240V A55 CL 1CT/10X10F | 56 mm | 55 mm | 97 mm |
| CLAS 60W E27 220-240V A55 CL 1CT/10X10F | 56 mm | 55 mm | 97 mm |
| CLAS 75W E27 220-240V A55 CL 1CT/10X10F | 56 mm | 55 mm | 97 mm |

| General Information | |
|-----------------------------|---------------|
| Cap-Base | E27 |
| Nominal lifetime | 1,000 hour(s) |
| Operating Position | UNIVERSAL |
| Light Technical | |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Voltage (Nom) | 220-240 V |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | A55 |

Light Technical

| Order Code | Full Product Name | Luminous Flux |
|--------------|---|---------------|
| 920052843329 | CLAS 25W E27 220-240V A55 CL 1CT/10X10F | 220 lm |
| 920054643329 | CLAS 60W E27 220-240V A55 CL 1CT/10X10F | 710 lm |
| 920055543329 | CLAS 75W E27 220-240V A55 CL 1CT/10X10F | 940 lm |
| 920119143329 | CLAS 15W E27 220-240V A55 CL 1CT/10X10F | 120 lm |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption |
|--------------|---|-------------------|
| 920052843329 | CLAS 25W E27 220-240V A55 CL 1CT/10X10F | 25 W |
| 920054643329 | CLAS 60W E27 220-240V A55 CL 1CT/10X10F | 60 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|---|-------------------|
| 920055543329 | CLAS 75W E27 220-240V A55 CL 1CT/10X10F | 75 W |
| 920119143329 | CLAS 15W E27 220-240V A55 CL 1CT/10X10F | 15 W |

