



FlexBlend heading the way to efficient and flexible furnished offices areas

FlexBlend, Suspended

Philips FlexBlend is an attractive family of surface-mounted and suspended luminaires, next to Flexblend recessed. The luminaire range enables building owners to advance their lighting operations by offering office-compliant lighting with a return on investment of less than three to four years. FlexBlend provides the required flexibility through its design adaptability. This offers the possibility to install the luminaires easily while in the field. so, if todays luminaire is suspended, tomorrow it can be adapted to be a surface-mounted installation at the venue. And vice versa. The surface-mounted and suspended luminaire range fits into many different office spaces, like open plan areas, corridors, receptions or meeting rooms. FlexBlend is offered in both lines and as standalone, using the same lighting module. This gives the option to use FlexBlend as standalone now, and tomorrow, as a line light. The controller is integrated into the luminaire. As technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations that can help optimise operations further. For this reason, FlexBlend has all connectivity and future-ready options available. As a System Ready luminaire, it can be paired with lighting management systems such as Philips SpaceWise, and to software-based lighting systems such as Interact Office wired (PoE) and Interact Office wireless and/or existing and upcoming sensor innovations. The luminaire range is therefore future-ready and can be delivered without any system components, and in the next phase, in the field, to be upgraded. An attractive opportunity for new installations and renovations.

FlexBlend, Suspended

Benefits

- Return of investment less than three years
- A flexible office, with application flexibility to the choice of luminaires to fit many office areas
- Future ready: scalable and ready to be connected to controls and lighting systems

Features

- Fully office-compliant (UGR <19, L65 < 3,000 cd/sm), light level according to office application requirements
- Homogenous and uniform light effect
- Various mounting options, dimensional variety and local options
- Integrated sensors
- Ready to be connected to software-based lighting systems, such as Interact Office

Application

- Offices
- Education
- Healthcare

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress and as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not followed and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe use and the product warranty will become void


Versions



FlexBlend Suspended SP340P MLO WH

FlexBlend, Suspended

Dimensional drawing



Product details




FlexBlend Suspended SP340P WH



FlexBlend Suspended SP340P SI

FlexBlend Suspended SP340P WH



FlexBlend Suspended SP340P
MLO WH

FlexBlend Surface Mounted
SM340C




FlexBlend Suspended SP340P WH



FlexBlend, Suspended

Product details




FlexBlend Suspended SP340P
MLO WH



FlexBlend Suspended SP340P BK

Polar Wide Diagrams



Polar Normal (separate) - SM340CI -
910925867129

