



For fresh looking food

MASTER TL-D Food

The TL-D Food lamp makes the appearance of meat and bakery products more fresh and tasty. It can be applied for food illumination in butcher shops, bakeries, supermarkets etc.

Benefits

- Makes the appearance of meat products and poultry more tasty

Features

- Spectral distribution optimal tuned to emphasize deep red colors such as those of meat and poultry


Application

- Food illumination (butcher shops, bakeries, supermarkets etc.)

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Food 18W/79 SLV/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
MASTER TL-D Food 30W/79 SLV/25	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm
MASTER TL-D Food 36W/79 SLV/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
MASTER TL-D Food 58W/79 SLV/25	28 mm	1,500 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

MASTER TL-D Food

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Food
Correlated Color Temperature (Nom)	3800 K
Color rendering index (CRI)	74
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg

Light Technical

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
928025402043	MASTER TL-D Food 30W/79 SLV/25	43 lm/W	1,300 lm
928048002043	MASTER TL-D Food 18W/79 SLV/25	41 lm/W	740 lm

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
928048502043	MASTER TL-D Food 36W/79 SLV/25	49 lm/W	1,750 lm
928049002043	MASTER TL-D Food 58W/79 SLV/25	48 lm/W	2,800 lm

Operating and Electrical

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928025402043	MASTER TL-D Food 30W/79 SLV/25	0.360 A	98 V	30.0 W
928048002043	MASTER TL-D Food 18W/79 SLV/25	0.360 A	59 V	18.0 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928048502043	MASTER TL-D Food 36W/79 SLV/25	0.440 A	103 V	36.0 W
928049002043	MASTER TL-D Food 58W/79 SLV/25	0.670 A	111 V	58.5 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000	
		h	
928025402043	MASTER TL-D Food 30W/79 SLV/25	37 kWh	
928048002043	MASTER TL-D Food 18W/79 SLV/25	23 kWh	

Order Code	Full Product Name	Energy Consumption kWh/1000	
		h	
928048502043	MASTER TL-D Food 36W/79 SLV/25	43 kWh	
928049002043	MASTER TL-D Food 58W/79 SLV/25	69 kWh	

MASTER TL-D Food

