



Product Description

MASTER TL-D Food

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Benefits

- Makes the appearance of food more tasty:
- Colour /79: makes the appearance of meat, meat products and poultry more tasty
- Colour /78: makes the appearance of bread, cake and pastry more tasty
- Colour /77: makes the appearance of meat, meat products and poultry more tasty

Features

- Spectral distribution optimal tuned to provide a good appearance of food:
- Colour /79: without having a red appearance themselves, the /79 lamps emphasize deep red colours such as those of meat and poultry
- Colour /78: without having a yellowish appearance themselves, the /78 lamps emphasize yellow colours such as those of bread, cake and pastry
- Colour /77: emphasize the deep red colours of meat to the maximum (even more than colour /79)
- Direct retrofit for all standard and Super 80 TL-D lamps operating on conventional or electronic gear

Application


- Food illumination (butcher shops, bakeries, supermarkets etc.)

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER TL-D Food

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Food 18W/79 SLV/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
MASTER TL-D Food 36W/79 SLV/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Food
Correlated Color Temperature (Nom)	3800 K
Color rendering index (CRI)	74
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg

Light Technical

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
928048002043	MASTER TL-D Food 18W/79 SLV/25	41 lm/W	740 lm

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
928048502043	MASTER TL-D Food 36W/79 SLV/25	49 lm/W	1,750 lm

Operating and Electrical

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928048002043	MASTER TL-D Food 18W/79 SLV/25	0.360 A	59 V	18.0 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928048502043	MASTER TL-D Food 36W/79 SLV/25	0.440 A	103 V	36.0 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000	
		h	
928048002043	MASTER TL-D Food 18W/79 SLV/25	23 kWh	

Order Code	Full Product Name	Energy Consumption kWh/1000	
		h	
928048502043	MASTER TL-D Food 36W/79 SLV/25	43 kWh	

MASTER TL-D Food

