



Product Description

MASTER TL Mini Super 80 Emergency Lighting

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Benefits

- Good colour rendering
- High efficacy, both initially and during lamp lifetime, with high lumen maintenance compared with standard lamps
- Small lamp dimensions enables system miniaturisation

Features

- 16 mm diameter tubes with high-quality fluorescent coating

Application

- Ideal for applications where space is limited but requiring better colour rendering and efficacy than standard colours:
- hall and staircase lighting in apartment buildings
- built into furniture, mirror and cupboard lighting
- emergency lighting

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTER TL Mini Super 80 Emergency Lighting

Versions



LPPR TL8MINI

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL Mini 8W/827 FAM/10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm
MST TL Mini 8W/840 FAM/10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

General Information	
Cap-Base	G5
Light Technical	
Color rendering index (CRI)	82
Luminous Efficacy (rated) (Nom)	59 lm/W
Luminous Flux	450 lm
Operating and Electrical	
Lamp Current (Nom)	0.145 A
Voltage (Nom)	56 V
Power Consumption	7.1 W
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Energy Consumption kWh/1000 h	8 kWh
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	3.0 mg

Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Correlated Color
		Coordinate X (Nom)	Coordinate Y (Nom)	Temperature (Nom)
70474027	MASTER TL Mini Super 80 8W/827 1FM/10X25CC	0.463	0.42	Incandescent White 2700 K
71642227	MASTER TL Mini Super 80 8W/840 1FM/10X25CC	0.38	0.38	Cool White (CW) 4000 K

MASTER TL Mini Super 80 Emergency Lighting

