


1 x TLED 11.3W 6500K 9290042426


1 x 2100 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.16
 Service downward 0.84


CIE flux code 38 66 87 84 100

UGRcen (4Hx8H, 0.25H) 25

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.42	0.40	0.39	0.40	0.40	0.39	0.31	0.30	0.25	0.28	0.24	0.21
0.80	0.52	0.48	0.47	0.50	0.48	0.47	0.39	0.37	0.32	0.35	0.30	0.27
1.00	0.60	0.55	0.54	0.57	0.55	0.54	0.46	0.43	0.38	0.41	0.36	0.32
1.25	0.68	0.62	0.60	0.65	0.62	0.60	0.52	0.50	0.44	0.47	0.42	0.38
1.50	0.74	0.67	0.65	0.71	0.68	0.65	0.58	0.54	0.49	0.51	0.47	0.42
2.00	0.83	0.75	0.72	0.80	0.76	0.72	0.66	0.62	0.57	0.59	0.55	0.49
2.50	0.90	0.80	0.77	0.86	0.81	0.77	0.71	0.67	0.63	0.64	0.60	0.54
3.00	0.95	0.83	0.79	0.90	0.85	0.81	0.75	0.71	0.67	0.67	0.64	0.58
4.00	1.01	0.88	0.85	0.96	0.90	0.85	0.81	0.76	0.73	0.72	0.69	0.63
5.00	1.06	0.91	0.88	1.00	0.94	0.88	0.84	0.79	0.77	0.75	0.73	0.66

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	9024	9080	9327	9777	10588	12032	14782
50.0	8594	8645	8865	9267	10013	11436	14435
55.0	8199	8239	8429	8772	9403	10768	13988
60.0	7837	7863	8024	8300	8822	10020	13393
65.0	7500	7523	7650	7855	8233	9168	12582
70.0	7201	7205	7314	7436	7647	8223	11514
75.0	6936	6929	7007	7057	7092	7196	9884
80.0	6711	6695	6754	6728	6609	6090	7497
85.0	6531	6504	6542	6464	6212	5097	4180
90.0	6401	6366	6391	6299	5938	4512	239

(cd/m²)

2024-11-29