


1 x TLED 13W 4000K 9290038061


1 x 2100 lm



Light output ratio	1.00
Service upward	0.23
Service downward	0.77

CIE flux code 37 65 86 77 100


UGRcen (4Hx8H, 0.25H)	25
-----------------------	----



Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)												
	0.80 0.80			0.70 0.70			0.50 0.50			0.30 0.30			0.00
	0.50 0.50			0.50 0.50			0.30 0.10			0.10 0.10			0.00
	0.30 0.10			0.30 0.20			0.10 0.10						0.00
0.60	0.41	0.39	0.39	0.38	0.37	0.30	0.28	0.23	0.26	0.22		0.18	
0.80	0.50	0.47	0.48	0.47	0.45	0.38	0.35	0.30	0.33	0.28	0.24		
1.00	0.58	0.54	0.56	0.54	0.52	0.44	0.41	0.36	0.38	0.34	0.29		
1.25	0.66	0.61	0.63	0.61	0.58	0.51	0.47	0.42	0.44	0.39	0.34		
1.50	0.72	0.66	0.69	0.66	0.63	0.56	0.52	0.47	0.48	0.44	0.38		
2.00	0.82	0.73	0.78	0.74	0.70	0.64	0.59	0.55	0.55	0.51	0.44		
2.50	0.88	0.78	0.84	0.79	0.75	0.69	0.64	0.60	0.60	0.56	0.49		
3.00	0.93	0.82	0.88	0.83	0.78	0.73	0.68	0.64	0.63	0.60	0.52		
4.00	1.00	0.86	0.94	0.88	0.83	0.78	0.73	0.70	0.67	0.65	0.57		
5.00	1.04	0.89	0.98	0.91	0.86	0.82	0.76	0.73	0.70	0.68	0.60		

Ceiling mounted



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	8397	8290	8467	8661	9180	10525	12720
50.0	8057	7923	8085	8186	8611	9948	12277
55.0	7871	7741	7748	7754	8075	9353	11758
60.0	7531	7328	7442	7347	7551	8719	11135
65.0	7138	7091	7193	6984	7047	8035	10344
70.0	7147	6888	6971	6665	6607	7322	9322
75.0	7017	6741	6825	6413	6215	6566	7953
80.0	6940	6637	6716	6227	5927	5829	6806
85.0	6912	6588	6674	6135	5774	5274	3404
90.0	6942	6602	6713	6161	5814	5515	3101

(cd/m²)

 (cd/m^2)