


1 x TLED 20W 4000K 9290042422


1 x 3700 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.16
 Service downward 0.84


CIE flux code 38 66 87 84 100

UGRcen (4Hx8H, 0.25H) 26

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.80	0.80	0.70	0.70	0.70	0.70	0.30	0.10	0.30	0.10	0.00	0.00
0.80	0.50	0.50	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
1.00	0.60	0.55	0.57	0.55	0.54	0.46	0.43	0.38	0.41	0.36	0.32	0.32
1.25	0.68	0.62	0.65	0.62	0.60	0.52	0.50	0.44	0.47	0.42	0.38	0.38
1.50	0.74	0.67	0.71	0.68	0.65	0.58	0.54	0.49	0.51	0.47	0.42	0.42
2.00	0.83	0.75	0.80	0.76	0.72	0.66	0.62	0.57	0.59	0.55	0.49	0.49
2.50	0.90	0.80	0.86	0.81	0.77	0.71	0.67	0.63	0.64	0.60	0.54	0.54
3.00	0.95	0.83	0.90	0.85	0.81	0.75	0.71	0.67	0.67	0.64	0.58	0.58
4.00	1.01	0.88	0.96	0.90	0.85	0.81	0.76	0.73	0.72	0.69	0.63	0.63
5.00	1.06	0.91	1.00	0.94	0.88	0.84	0.79	0.77	0.75	0.73	0.66	0.66

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	12720	12806	13162	13805	14960	17012	20921
50.0	12114	12193	12510	13087	14151	16178	20446
55.0	11557	11621	11897	12390	13293	15241	19831
60.0	11046	11091	11327	11725	12476	14190	19010
65.0	10572	10612	10800	11099	11647	12992	17887
70.0	10151	10164	10327	10510	10823	11664	16407
75.0	9776	9776	9894	9976	10043	10218	14136
80.0	9460	9445	9539	9514	9364	8661	10796
85.0	9206	9177	9241	9144	8809	7263	6128
90.0	9022	8983	9029	8915	8428	6453	422

(cd/m²)

2024-11-29