

# PHILIPS

Bulb 50W A60 E27

LED

3000K

460lm

8000h

8718696845295



## State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

# Highlights

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no

ultra-violet light means that fabric and items under this light won't fade.

## Contains no mercury

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Dimmable: No

## Bulb dimensions

- Height: 10.4 cm
- Width: 5.8 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 8,000 hour(s)

## Light characteristics

- Color rendering index (CRI): 70
- Color temperature: 3000 K
- Nominal luminous flux: 460 lm
- Warm-up time to 60% light: instant full light

## Other characteristics

- Efficacy: 92 lm/W

## Packaging information

- Product family: Mainstream

## Power consumption

- Power factor: >0.5
- Voltage: 220–240 V
- Wattage: 5 W
- Wattage equivalent: 50 W

## Product dimensions and weight

- Length: 10.4 cm

## Technical specifications

- Frequency: 50–60 Hz

## Packaging dimensions and weight

**[ESS LEDBulb 5W E27 3000K 230V 1CT/12 MY]**

- EAN/UPC – product: 8718696845295
- Net weight: 0.05 kg
- Gross weight: 0.06 kg
- Height: 9.8 cm
- Length: 5.7 cm
- Width: 5.7 cm
- Material number (12NC): 929001899037

## Packaging dimensions and weight

**[ESS LEDBulb 5W E27 3000K 230V 1CT/12 MY]**

- EAN/UPC – product: 8718696845295
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 10.7 cm
- Length: 6.1 cm
- Width: 6.1 cm
- Material number (12NC): 929002298637



Issue date: 2024-03-29  
Version: 0.515

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)