



## Motion Sensor

The WiZ wireless indoor sensor sets your lights to turn on and off according to motion detection. Put it at the entrance or corridor and trigger on your desired light modes just by walking by, set it to turn off or to minimum brightness after you leave the room. It controls all the lights in a room and has a motion detection range of up to 3 meters. Set the sensor to trigger different light modes during different times of the day in the WiZ app (e.g. warm white in the evening or nightlight after bedtime).

## PRODUCT HIGHLIGHTS

- Battery operated
- IP20/Plastic/White
- Works with all WiZ Connected products



### Easy wireless installation

Battery-powered, no wire necessary. Make it a quick and easy install with screws on the ceiling / wall, or simply leave it on a desk.



### Flexible motion settings for your convenience

Set your lights to turn on a preferred brightness or specific mode, such as nightlight or daylight. You can configure an action for your lights, with a specified delay, and when no motion is detected.



### Set the right light for the right time

Set sensors to activate your favorites light modes at different times during the day, by setting specific Rhythms for a room in the WIZ app.



### Compatible with all "Connected by WiZ" lights

This WiZ control accessory is designed to control all kinds of lights in the WiZ ecosystem. You can use it to control any lights from any brand as long as it's "Connected by WiZ."



### Trigger lights with motion

Set your lights to turn on/off or change brightness and color whenever they detect any motion. This sensor connects directly to your WiZ lights and works even when the Wi-Fi is down.



### Wide connection range of 15m / 50ft

This motion sensor connects with WiZ lights placed within a range of up to 15 meters or 50 feet in a normal indoor environment with partitions and walls.



# SPECIFICATIONS

## DESIGN AND FINISHING

Color: White  
Material: Plastic

## EXTRA FEATURE/ACCESSORY INCL.

Batteries included: No  
Detection Area: 0 - 3 m  
Control Distance: 15 m

## POWER CONSUMPTION

Voltage: 3 V

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.057 kg  
Overall height: 50 mm  
Overall length: 62 mm  
Overall width: 62 mm

## SERVICE

Warranty: 1 year(s)

## TECHNICAL SPECIFICATIONS

Battery type: AA  
IP code: IP20 | Finger-protected  
Class of protection: Class III - Safe  
Extra Low Voltage

## WHAT'S SUPPORTED

Compatible with Effects: Yes  
WiFi: Wireless G  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth  
WiFi (2.4GHz)

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8719514261501  
Net weight: 0.1 kg  
Gross weight: 0.11 kg  
Height: 13 cm  
Length: 7 cm  
Width: 7 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.