



NFC TAG 4 PIECES

WiZ NFC tags can help you set your favorite light modes quickly. Simply stick these customizable tags and tap them with your phone. You can personalize the tags to turn lights on or off, trigger focus mode for working at home, set lights to party mode to boogie down with your friends, or any other setting you desire. Quick and easy, no batteries required.


PRODUCT HIGHLIGHTS

- No battery required
- IP20/PET/White
- Works with all Connected by WiZ products




Place or stick your WiZ tags

Stick the adhesive-backed WiZ NFC tags in a convenient location indoors—for example, on a wall or on a desk.



Quick and easy control for your WiZ lights

Simply set up these NFC tags in the WiZ app, then tap them with your smartphone to activate and control your lights. Quick and easy, no batteries needed.




Customize tag actions

Using the WiZ app, assign an action to each tag. Turn WiZ lights on or off, trigger focus mode when working from home, activate party mode and boogie down with your friends, or select any other setting you desire.



Works with the WiZ app

This NFC tag works with WiZ app so you can control all kinds of lights in the WiZ ecosystem. Any lights, as long as they are "Connected by WiZ".



Personalize your WiZ tags with your own stickers

Apply the stickers designed by WiZ to your NFC tags so that you can distinguish them at a glance. Or use the blank stickers to create your own labels and designs.



SPECIFICATIONS

DESIGN AND FINISHING

Color: White
Material: PET

EXTRA FEATURE/ACCESSORY INCL.

Batteries included: No
Control Distance: 0.015 m

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.0008 kg
Height: 0.1 cm
Length: 2.5 cm
Width: 2.5 cm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Diameter: 25 mm
Battery type: NA
IP code: IP20
Class of protection: NA

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169072411
Net weight: 0.76 kg
Gross weight: 0.79 kg
Height: 10.1 cm
Length: 3.1 cm
Width: 7.6 cm
Material number (12NC):
929003266901



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.