

PHILIPS

LED PL-C

LED

1400lm

4000K

G24d

8721103042767



Easy upgrade from current conventional PLC downlight fixtures

LED PLC lamps deliver incredible energy savings over a long life time by replacing old fluorescent tubes with modern efficient LED technology. Perfect for general circulation areas (corridors, stairways, hallways).

Choose for a sustainable solution

- Long life tubes - Lasts up to 30 years
- Saves up to 80% Energy

Light beyond illumination

- Instant on

Highlights

30,000-hour rated average life



With a lifetime of up to 30,000 hours, you can reduce the hassle of

frequently replacing your light tubes and enjoy a perfect lighting solution for over 30 years.

Instant on

Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: PL-C
- Socket: G24d
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

Bulb dimensions

- Height: 13.5 cm
- Width: 4.45 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 30,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 240 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Nominal luminous flux: 1400 lm

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 140 lm/W

Packaging information

- EAN: 8721103042767
- EOC: 872110304276700
- Product title: LED PLC 10W 840 2P G24d

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage equivalent: 26 W
- Power Consumption: 10 W

Product dimensions and weight

- Length: 13.5 cm

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC – product: 8721103042767
- Net weight: 0.06 kg
- Gross weight: 0.14 kg
- Height: 13.5 cm
- Length: 4.5 cm
- Width: 4.5 cm



Issue date: 2025-06-14
Version: 0.87

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com