


MAG L FLOOD 7W 530LM 1 x 9290032068 3000K


1 x 530 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 61 89 98 100 100

UGRcen (4Hx8H, 0.25H) 24

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.57	0.54	0.56	0.55	0.54	0.47	0.47	0.43	0.46	0.42	0.41	0.41
0.80	0.68	0.63	0.67	0.65	0.63	0.56	0.56	0.51	0.55	0.51	0.49	0.49
1.00	0.76	0.71	0.75	0.72	0.70	0.64	0.63	0.59	0.62	0.59	0.57	0.57
1.25	0.84	0.77	0.83	0.80	0.77	0.71	0.70	0.66	0.69	0.66	0.64	0.64
1.50	0.90	0.82	0.88	0.85	0.81	0.76	0.75	0.71	0.74	0.71	0.69	0.69
2.00	0.99	0.89	0.97	0.92	0.88	0.84	0.82	0.79	0.81	0.78	0.76	0.76
2.50	1.05	0.93	1.03	0.97	0.92	0.88	0.87	0.84	0.86	0.83	0.81	0.81
3.00	1.09	0.96	1.06	1.00	0.95	0.92	0.90	0.88	0.89	0.87	0.84	0.84
4.00	1.14	0.99	1.11	1.04	0.98	0.95	0.94	0.92	0.92	0.91	0.88	0.88
5.00	1.17	1.01	1.14	1.06	1.00	0.98	0.96	0.94	0.94	0.93	0.90	0.90

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	23174	23191	23277	23425	23630	23878	24156
50.0	19474	19491	19576	19724	19928	20177	20456
55.0	16095	16111	16195	16340	16542	16788	17067
60.0	13362	13379	13461	13607	13809	14057	14340
65.0	10668	10684	10765	10907	11105	11351	11634
70.0	8845	8862	8945	9094	9303	9565	9869
75.0	7518	7537	7630	7797	8035	8338	8697
80.0	6275	6297	6408	6609	6902	7287	7761
85.0	3738	3760	3872	4082	4406	4866	5493
90.0	143	146	159	190	257	445	2189

(cd/m²)

2022-03-10