



## Filament Globe Amber 50W G125 E27

We challenge you to find a light bulb more elegant. These globe-shaped, amber-coated LED smart bulbs create a vintage vibe for your decorative fixtures or wherever you want a touch of chic. Choose from hundreds of shades of white light from cozy to cool, or schedule to automatically adjust to match your ever-changing needs and moods. All Wi-Fi controllable using the WiZ app, WiZ remote, or your voice.

## PRODUCT HIGHLIGHTS

- Tunable white smart bulb
- Up to 640 lumens
- Easy plug and play
- Control with app or voice



### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



### Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



### Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.




### Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



### Dim your smart lights even without a dimmer

Simply adjust lights to your desired brightness level using your smartphone, the WiZ control accessory or just your voice. No need to install an expensive dimmer!



### Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Lamp shape: G125  
Socket: E27  
Type of glass: Amber  
Dimmable: Yes

## BULB DIMENSIONS

Weight: 0.115 kg

## DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 20,000  
Nominal lifetime: 15,000

## EXTRA FEATURE/ACCESSORY INCL.

LED integrated: Yes  
Solar Energy: No  
Warm glow dimmable light: No

## LIGHT CHARACTERISTICS

Color consistency: 6 SDCM  
Color rendering index (CRI):  $\geq 90$   
Color temperature: 2000-5000 K  
Light Color Category: Tunable white  
Nominal luminous flux: 640 lm  
Starting time:  $< 0.5$  s  
Warm-up time to 60% light: instant full light  
Luminous Efficacy (rated) (Nom): 91

## OTHER CHARACTERISTICS

Lamp current: 43 mA

## PACKAGING INFORMATION

EAN: 8718699786816  
EOC: 871869978681602  
Product title: Wi-Fi BLE 50W G125  
E27 920-50 Amb 1PF/6

## POWER CONSUMPTION

Power factor: 0.5  
Voltage: 220-240 V  
Wattage equivalent: 50 W  
Energy Efficiency Label (EEL): F  
Power: 7 W  
Energy Consumption kWh/1000 h: 7

## PRODUCT DIMENSIONS AND WEIGHT

Overall height: 180 mm  
Overall length: 180 mm  
Overall width: 125 mm

## RATED VALUES

Rated lifetime: 15,000  
Rated luminous flux: 640 lm  
Rated power: 7 W

## TECHNICAL SPECIFICATIONS

Frequency: 50-60  
Bulb technology: LED  
EPREL Registration Number: 1901132  
Flux measurement reference: Sphere

## THE BULB

Software upgradable: Yes

## WHAT'S SUPPORTED

Compatible with Effects: Yes  
WiFi: 802.11b/g/n  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Compatible operating systems: iOS  
Android  
Communication protocol: Bluetooth  
WiFi (2.4GHz)  
Compatibility with 3rd party systems:  
Alexa Enki Google Home Homey  
IFTTT Matter Samsung Smartthings  
Siri Shortcuts  
Matter functionality: Via 3rd party hubs (Wi-Fi)

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8718699786816  
Net weight: 0.12 kg  
Gross weight: 0.2 kg  
Height: 22.5 cm  
Length: 12.8 cm  
Width: 12.8 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.