



## Candle 40W C37 E14

Who doesn't love the look of a candle? These energy-friendly candle-shape LED bulbs give you all the elegance of candlelight along with something that no standard candle could ever do: hundreds of shades of white light that you can tune to match your ever-changing needs and moods. Schedule cool light when you need to focus, or cozy light when you want to relax—whatever works for you to live your best, most enjoyable life at home. All Wi-Fi controllable using the WiZ app, WiZ remote, or your voice.

## PRODUCT HIGHLIGHTS

- Tunable white smart bulb
- Up to 470 lumens
- Easy plug and play
- Control with app or voice




### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



### Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



### Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



### Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



### Create your perfect outdoor light Scene

Mix different color and white light modes to create the perfect light ambience for your perfect garden moments. Save your scene and select it anytime with app, voice or control accessory.



### Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Lamp shape: C37  
Socket: E14  
Type of glass: Frosted  
Dimmable: Yes

## BULB DIMENSIONS

Weight: 0.045 kg

## DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 15,000

## EXTRA FEATURE/ACCESSORY INCL.

LED integrated: Yes  
Solar Energy: No  
Warm glow dimmable light: No

## LIGHT CHARACTERISTICS

Color consistency: 6 SDCM  
Color rendering index (CRI):  $\geq 90$   
Color temperature: 2700-6500 K  
Light Color Category: Tunable white  
Nominal luminous flux: 470 lm  
Starting time:  $< 0.5$  s  
Warm-up time to 60% light: instant full light  
Luminous Efficacy (rated) (Nom): 95

## OTHER CHARACTERISTICS

Lamp current: 40 mA

## PACKAGING INFORMATION

EAN: 8718699787073  
EOC: 871869978707301  
Product title: Wi-Fi BLE 40W C37 E14 927-65 TW 1PF/6

## POWER CONSUMPTION

Power factor: 0.51  
Voltage: 220-240 V  
Wattage equivalent: 40 W  
Energy Efficiency Label (EEL): F  
Power: 4.9 W  
Energy Consumption kWh/1000 h: 5

## PRODUCT DIMENSIONS AND WEIGHT

Overall height: 116 mm  
Overall length: 116 mm  
Overall width: 39 mm

## RATED VALUES

Rated lifetime: 15,000  
Rated luminous flux: 470 lm  
Rated power: 4.9 W

## TECHNICAL SPECIFICATIONS

Frequency: 50-60  
Bulb technology: LED  
EPREL Registration Number: 1901096  
Flux measurement reference: Sphere

## THE BULB

Software upgradable: Yes

## WHAT'S SUPPORTED

Compatible with Effects: Yes  
WiFi: 802.11b/g/n  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Compatible operating systems: iOS  
Android  
Communication protocol: Bluetooth  
WiFi (2.4GHz)  
Compatibility with 3rd party systems: Alexa Enki Google Home Homey IFTTT Matter Samsung Smartthings Siri Shortcuts  
Matter functionality: Via 3rd party hubs (Wi-Fi)

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8718699787073  
Net weight: 0.05 kg  
Gross weight: 0.09 kg  
Height: 16 cm  
Length: 7 cm  
Width: 7 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.