



Candle 40W C37 E14

Candles are delightful, but they can do only one thing: produce candlelight. These full-color candle-shape LED bulbs, on the other hand, can do 16.7 million things. Choose the perfect hue for whatever you've got going on—whether it's a rollicking party, an elegant dinner, or chilling on the couch with a good movie—or create schedules to automatically transition to the perfect ambiance as your needs and moods change. All Wi-Fi controllable using the WiZ app, WiZ remote, or even your voice.

PRODUCT HIGHLIGHTS

- Full color smart bulb
- Up to 470 lumens
- Easy plug and play
- Control with app or voice



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.




Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: C37
Socket: E14
Type of glass: Frosted
Dimmable: Yes

BULB DIMENSIONS

Weight: 0.045 kg

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

LED integrated: Yes
Solar Energy: No
Warm glow dimmable light: No

LIGHT CHARACTERISTICS

Color consistency: 6 SDCM
Color rendering index (CRI): ≥ 90
Color temperature: 2200-6500 K
Light Color Category: Full color
Nominal luminous flux: 470 lm
Starting time: < 0.5 s
Warm-up time to 60% light: instant full light
Luminous Efficacy (rated) (Nom): 95

OTHER CHARACTERISTICS

Lamp current: 40 mA

PACKAGING INFORMATION

EAN: 8718699787097
EOC: 871869978709701
Product title: Wi-Fi BLE 40W C37 E14
922-65 RGB 1PF/6

POWER CONSUMPTION

Power factor: 0.51
Voltage: 220-240 V
Wattage equivalent: 40 W
Energy Efficiency Label (EEL): F
Power: 4.9 W
Energy Consumption kWh/1000 h: 5

PRODUCT DIMENSIONS AND WEIGHT

Overall height: 116 mm
Overall length: 116 mm
Overall width: 39 mm

RATED VALUES

Rated lifetime: 15,000
Rated luminous flux: 470 lm
Rated power: 4.9 W

TECHNICAL SPECIFICATIONS

Frequency: 50-60
Bulb technology: LED
EPREL Registration Number: 1877836
Flux measurement reference: Sphere

THE BULB

Software upgradable: Yes

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: 802.11b/g/n
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Compatible operating systems: iOS
Android
Communication protocol: Bluetooth
WiFi (2.4GHz)
Compatibility with 3rd party systems:
Alexa Enki Google Home Homey
IFTTT Matter Samsung Smartthings
Siri Shortcuts
Matter functionality: Via 3rd party hubs (Wi-Fi)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8718699787097
Net weight: 0.05 kg
Gross weight: 0.09 kg
Height: 16 cm
Length: 7 cm
Width: 7 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.