

PHILIPS

Bulb 8W (Eq.60W)
A60 B22

Smart LED

Warm white


Plastic

Easy plug and play

Control with WiZ app or voice



8719514372580



Get cozy warm white light

Bring warm white light to your B22 fittings with the Philips Smart LED dimmable smart bulb. This bulb is WiZ connected. Use with your existing Wi-Fi to control with the WiZ app or your voice.

Easy setup

- Easy plug and play. Works with your existing Wi-Fi.

Smart control

- Control anywhere with your smartphone.
- Voice control with Google Assistant, Alexa or Siri Shortcuts

Smart features

- Smart dimming via app, voice or dimmer
- Automate your light with schedules
- Energy monitoring

Light modes

- Customize Scenes with preset dynamic light modes.
- Soft warm white light

Highlights

Easy plug and play

WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

Control from anywhere

Control your WiZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WiZ app is available for iOS and Android.

Voice Control

Get hands-free control of your lights by using your voice and Google Assistant, Amazon Alexa or Siri Shortcuts. Use simple voice commands to turn lights on or off, brighten and dim, change color, and set custom light Scenes.

Smart dimming

Dim your lights to your desired brightness level via your smartphone, the WiZmote or your voice. No need to install an expensive dimmer.

Automate your light with schedules

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

Energy monitoring

The WiZ app keeps records of the energy consumption of your lights. View your weekly or daily report and plan your lighting wisely for an optimized energy consumption at home.

Customized Scenes

Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, WiZmote or voice.

Soft warm white light

Create a cozy atmosphere with warm white light. A smart light that simply adapts to your daily activities

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: A60
- Socket: B22
- Type of glass: Frosted
- Bulb Finish: Frosted
- Dimmable: Yes

Bulb dimensions

- Weight: 0.06 kg

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

Extra feature/accessory incl.

- LED integrated: Yes
- Solar Energy: No
- Warm glow dimmable light: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): ≥90
- Color temperature: 2700 K
- Light Color Category: Soft White
- Nominal luminous flux: 806 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Luminous Efficacy (rated) (Nom): 100

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 70 mA

Packaging information

- EAN: 8719514372580
- EOC: 871951437258000
- Product title: PHI WFB 60W A60 B22 927 DIM 1PF/6

Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage equivalent: 60 W
- Energy Efficiency Label (EEL): F
- Power: 8 W
- Energy Consumption kWh/1000 h: 8

Product dimensions and weight

- Overall height: 120 mm
- Overall length: 120 mm
- Overall width: 60 mm

Rated values

- Rated lifetime: 25,000
- Rated luminous flux: 806 lm
- Rated power: 8 W

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50–60
- Bulb technology: LED
- EPREL Registration Number: 584556

What's supported

- Compatible with Effects: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with 3rd party systems: Alexa, Enki, Google Home, Homey, IFTTT, Matter, Samsung Smartthings, Siri Shortcuts

Packaging dimensions and weight

- EAN/UPC - product: 8719514372580
- Net weight: 0.06 kg
- Gross weight: 0.1 kg
- Height: 16 cm
- Length: 7 cm
- Width: 7 cm



Issue date: 2026-04-08
Version: 0.425

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com