

# PHILIPS

Bulb 50W A60 B22  
x6

LED

6500K

806lm

15000h

8719514472372



## State-of-the-art LED light bulb for the home

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### **Choose a simple replacement for your old bulbs**

- Similar shape and size as standard incandescent bulb

### **Choose for a sustainable solution**

- You can trust what the Philips packaging is saying.

### **Create the right light for your home**

- A simple LED for everyday use

# Highlights

## Replaces standard incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

## A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Beam angle: 180
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 806 lm
- Luminous Efficacy (rated) (Nom): 89

## Miscellaneous

- EyeComfort: No

## Packaging information

- EAN: 8719514472372
- EOC: 871951447237200
- Product title: LEDBulb 9W B22 6500K 230V 6CT/6 AU

## Power consumption

- Power factor: 0.51
- Voltage: AC 220-240 V
- Wattage equivalent: 50
- Power: 9

## Product dimensions and weight

- Overall height: 105 mm
- Overall length: 105 mm
- Overall width: 60 mm

## Technical specifications

- Frequency: 50-60
- Bulb technology: LED

## Packaging dimensions and weight

- EAN/UPC - product: 8719514472372
- Net weight: 0.13 kg
- Gross weight: 0.22 kg
- Height: 11.7 cm
- Length: 12.5 cm
- Width: 18.7 cm



Issue date: 2026-03-21  
Version: 0.206

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)