



State-of-the-art LED light bulb for the home

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

Choose a simple replacement for your old bulbs

· Similar shape and size as standard incandescent bulb

Choose for a sustainable solution

· You can trust what the Philips packaging is saying.

Create the right light for your home

· A simple LED for everyday use

Highlights

Replaces standard incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won $\phi_{\overline{1}}$ t fade.

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non directional bulb

· Socket: B22

Bulb Finish: FrostedDimmable: NoBulb Material: Plastic

Durability

Number of switch cycles: 50,000

· Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

• Beam angle: 180 degree(s)

· Color rendering index (CRI): 80

· Color temperature: 6500 K

· Nominal luminous flux: 806 lm

 Luminous Efficacy (rated) (Nom): 89 lm/W

Miscellaneous

· EveComfort: No

Packaging information

• EAN: 8719514472372

• EOC: 871951447237200

• Product title: LEDBulb 9W B22 6500K

230V 6CT/6 AU

Power consumption

Power factor: 0.51Voltage: AC 220-240 VWattage equivalent: 50 W

• Power Consumption: 9 W

Product dimensions and weight

Overall height: 105 mmOverall length: 105 mm

· Overall width: 60 mm

Technical specifications

• Frequency: 50-60

Packaging dimensions and weight

• EAN/UPC - product: 8719514472372

Net weight: 0.13 kg

Gross weight: 0.22 kg

• Height: 11.7 cm

· Length: 12.5 cm

• Width: 18.7 cm



Issue date: 2025-11-05 Version: 0.206

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips