

PHILIPS

Bar linear light

Smart LED

Full color

Versatile bar light

Easy plug and play



8719514435179



Make your tiny spaces light with ambience

If you have a shelf or corner that needs accent lighting, try our Bar light. This slim bar radiates plenty of colors and is easy to fit in small spaces. Simply tilt it on one of its sides to adjust the light angle. Do you prefer a longer light? Connect a second bar to double the effect.

Easy setup

- Easy plug and play

Smart control

- Control from anywhere with your smartphone
- Go hands-free with voice control

Smart features

- Automate your light with schedules

Light modes

- Millions of colors and dynamic light modes
- Tunable warm to cool white and preset modes
- Customize Scenes with preset dynamic light modes

Form factor

- A slender design for versatile use

Highlights

Easy plug and play



WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

Control from anywhere



Control your WiZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WiZ app is available for iOS and Android.

Go hands-free with voice control



Control your lights with just the sound of your voice, simply enable integration with Google, Alexa or add to your Siri shortcuts.

Automate your light with schedules

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

Millions of colors and dynamic light modes



Choose from a palette of millions of light colors to create an amazing atmosphere in your home. Enjoy the subtle differences that our dynamic light effects glow your environment.

Tunable warm to cool white and preset modes




Choose from a wide range of energizing cool white to soft warm white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

Customized Scenes



Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, remote or voice.

Versatile bar light



Tilt this light bar at an angle to shine its colorful light on a cabinet or shelf. Amplify beautiful accent lighting in any corner or wall by connecting two light bars. Cable included.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Rectangle
- Dimmable: Yes

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- On/off switch on wire: No
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): ≥ 80
- Warm-up time to 60% light: < 2

Miscellaneous

- Especially designed for: Functional
- EyeComfort: Yes

Other characteristics

- Lamp current: 75 mA
- Efficacy: 72 lm/W

Power consumption

- Power factor: 0.7
- Voltage: 220-240 V

Product dimensions and weight

- Net weight: 0.7 kg
- Height: 4.2 cm
- Length: 60 cm
- Width: 4.5 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: 800
- Light color: 2200-6500 (RGB)
- Wattage bulb included: 10.5
- IP code: IP20
- Class of protection: Class II

The bulb

- Communication protocol: Bluetooth, WiFi (2.4GHz)

What's supported

- Compatible with Effects: Yes
- WiFi: Wireless G
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999

Packaging dimensions and weight

- EAN/UPC – product: 8719514435179
- Net weight: 0.7 kg
- Gross weight: 0.9 kg
- Height: 8.7 cm
- Length: 5.9 cm
- Width: 40.5 cm



Issue date: 2025-06-06
Version: 0.89

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com