

# PHILIPS

Bulb 60W A60 E27

Smart LED

Tunable white smart bulb

Up to 806 lumens

Easy plug and play

Control with app or voice

8720169302976



## Smart lighting for your daily living

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### Easy setup

- Easy plug and play

### Smart control

- Control from anywhere with your smartphone
- Go hands-free with voice control

### Smart features

- Automate your light with schedules
- Energy monitoring
- Exclusive SpaceSense™ light that turns on with movement

### Light modes

- Tunable warm to cool white and preset modes


# Highlights

## Easy plug and play



WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

## Control from anywhere



Control your WiZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WiZ app is available for iOS and Android.

## Go hands-free with voice control



Control your lights with just the sound of your voice, simply enable integration with Google, Alexa or add to your Siri shortcuts.

## Automate your light with schedules

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

## Energy monitoring



The WiZ app keeps records of the energy consumption of your lights. View your weekly or daily report and plan your lighting wisely for an optimized energy consumption at home.

## Light automation with SpaceSense



WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.

## Tunable warm to cool white and preset modes



Choose from a wide range of energizing cool white to soft warm white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: A60
- Socket: E27
- Type of glass: Frosted
- Dimmable: Yes
- Bulb Finish: Frosted

## Bulb dimensions

- Weight: 0.05 kg

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

## Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI):  $\geq 80$
- Color temperature: 2700–6500 K
- Light Color Category: Tunable white
- Nominal luminous flux: 806 lm
- Starting time:  $< 0.5$  s
- Warm-up time to 60% light: instant full light
- Luminous Efficacy (rated) (Nom): 100 lm/W

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 65 mA

## Packaging information

- EAN: 8720169302976
- EOC: 872016930297600
- Product title: PHI WFB 60W A60 E27 827-65 TW 1CT/6

## Power consumption

- Power factor: 0.5
- Voltage: AC 220–240 V
- Power Consumption: 8 W

## Product dimensions and weight

- Overall height: 111 mm
- Overall length: 111 mm
- Overall width: 60 mm

## Rated values

- Rated lifetime: 25,000
- Rated luminous flux: 806 lm
- Rated power: 8 W

## Service

- Warranty: 2 year(s)

## Technical specifications

- Frequency: 50–60

## What's supported

- Compatible with Effects: Yes
- WiFi: Wireless G
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Communication protocol: Bluetooth, WiFi (2.4GHz)

## Packaging dimensions and weight

- EAN/UPC – product: 8720169302976
- Net weight: 0.05 kg
- Gross weight: 0.08 kg
- Height: 13 cm
- Length: 7 cm
- Width: 7 cm



Issue date: 2025-08-30  
Version: 0.95

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)