

# PHILIPS

Candle 25W B35 E14

LED

2700K

250lm

15000h

220-240 V



8718696454855



## Clear LED candle adds comfort sparkle to your home

Experience warm white LED light

### Sustainable choice

- Lasts up to 15 years
- Very low energy consumption; saving at least 80%

### Create a warm atmosphere

- True incandescent-like warm white light (2700 K)

### Instant light (LED)

- Instant light when switched on

# Highlights

## **Lasts up to 15 years**

With a lifetime of up to 15.000 hours, this Philips LED lamp will ensure your desired atmosphere for up to 15 years.\*

## **Very low energy consumption**



When you switch to a Philips LED light bulb, you immediately use up to 80% less energy without sacrificing light output and quality.

## **Warm white light (2700K)**

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

## **Instant light when switched on**

No need to wait: Philips LED light bulbs provide their full level of brightness immediately upon switching on.

# Specifications

## Bulb characteristics

- Shape: Candle
- Lamp shape: Non directional candle
- Socket: E14
- Type of glass: Clear
- Lamp shape code: B35
- Dimmable: No
- Bulb Finish: Clear

## Bulb dimensions

- Height: 10.6 cm
- Width: 3.5 cm

## Durability

- Number of switch cycles: 50000
- Nominal lifetime: 15000 hour(s)

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 250 lm
- Warm-up time to 60% light: instant full light

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

## Packaging information

- Product family: EyeComfort

## Power consumption

- Power factor: 0.4
- Voltage: 220-240 V
- Wattage: 4 W
- Wattage equivalent: 25 W

## Product dimensions and weight

- Length: 10.6 cm

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions and weight

- EAN/UPC – product: 8718696454855
- Net weight: 0.04 kg
- Gross weight: 0.05 kg
- Height: 14 cm
- Length: 4.5 cm
- Width: 4.5 cm
- Material number (12NC): 929001142207



Issue date: 2024-04-12  
Version: 0.649

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)