
PHILIPS

Smart LED A19 Bulb, 800 lm

Smart LED

- Tunable white light
- Low dimming
- Smart automations
- Control with WiZ app or voice

046677562694



Make your home lighting smarter

Enjoy complete control over your lighting with tunable white light that you can adjust effortlessly from cool, focus-enhancing tones (6500 K) to warm, relaxing hues (2700 K). Fine-tune the brightness from full intensity down to just 1% to create the perfect ambiance for any activity, while built-in automations let your lights follow your daily routine.

Smart control
- Connected by WiZ
- Smart controls

Smart features
- SpaceSense motion detection
- Smart automations

Smart devices
- Matter certified

Light modes
- Tunable white light
- Low dimming

Highlights

Connected by WiZ


Control your lights using the WiZ app, accessories, or voice commands via your smart home assistant; compatible with Alexa and Google Home.

Smart automations




Schedule your lights to work in sync with your routine, switching on automatically when you wake up, or switching off when nobody's home to save energy.

Low dimming



Dim your light smoothly from full brightness down to 1% to achieve the right level of light for whatever you're doing.

Smart controls




Control your lights using the WiZ app, accessories, or voice commands via your smart home assistant; compatible with Alexa and Google Home.

Matter certified

Control your way using your preferred smart home assistant—Matter compatible for seamless integration with Alexa, Google Home, and Apple Home.

SpaceSense motion detection



Turn your lights into motion sensors using integrated SpaceSense technology, so that they switch on automatically when you enter the room—all you need are two or more Connected by WiZ lights or devices.

Tunable white light



Easily adjust from cool, bluish hues that enhance visibility and focus to soft, warmer tones for relaxing in the evening (CCT range 2200 K–6500 K).

Specifications

Bulb characteristics
- Intended use: Indoor
- Lamp shape: A19
- Socket: E26
- Type of glass: Frosted
- Bulb Finish: Frosted
- Dimmable: Yes

Bulb dimensions
- Weight: 0.05 kg

Design and finishing
- Color: White
- Material: Plastic

Durability
- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Ambient temperature range: -4 to +113 °F
- Nominal lifetime: 25,000

Extra feature/accessory incl.
- Adjustable spot head: No
- Choose your color: Yes
- Fully weatherproof: No
- LED integrated: Yes
- Solar Energy: No
- Warm glow dimmable light: No

Light characteristics
- Beam angle: 200
- Color consistency: 4 SDCM
- Color rendering index (CRI): 90
- Color temperature: 2200-6500 K
- Light Color Category: Tunable white
- Nominal luminous flux: 800 lm
- Starting time: <1 s
- Warm-up time to 60% light: instant full light
- Luminous Efficacy (rated) (Nom): 90

Miscellaneous
- Especially designed for: Bedroom, Dining Room, Living Room, Children's room
- EyeComfort: Yes

Other characteristics
- Lamp current: 100 mA

Packaging information
- EAN: 046677562694
- EOC: 562694
- Product title: 8.8A19/Wi-Fi BLE Tunable/927-65 4/1PF

Power consumption
- Power factor: 0.7
- Voltage: AC 120 V
- Wattage equivalent: 60 W
- Power: 8.8 W
- Energy Consumption kWh/1000 h: 11

Product dimensions and weight
- Overall height: 7/16 inch
- Overall length: 7/16 inch
- Overall width: 1/4 inch

Rated values
- Rated lifetime: 25,000
- Rated luminous flux: 800 lm
- Rated power: 8.8 W

Service
- Warranty: 3 year(s)

Technical specifications
- Frequency: 60
- Diameter: 2-3/8 inch
- Bulb technology: LED
- Light color: Tunable white light
- IP code: IP20

The bulb
- Diameter: 2-3/8 inch
- Software upgradable: Yes

What's supported

- Compatible with Effects: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum 60 months from date of purchase from an authorized reseller
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with 3rd party systems: Alexa, Enki, Google Home, Homey, IFTTT, Matter, Samsung Smartthings, Siri Shortcuts
- Matter functionality: Via 3rd party hubs (Wi-Fi)

Packaging dimensions and weight

- EAN/UPC - product: 046677562694
- Net weight: 0.05 kg
- Gross weight: 0.11 kg
- Height: 17 cm
- Length: 7.2 cm
- Width: 9.9 cm

Issue date: 2026-07-11
Version: 0.110

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com