

# PHILIPS

Filament Bulb Clear  
40W T10 E26

LED

2700K

330lm

15000h

046677572501



## Beautify your home with Philips LED globe bulbs

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your clear incandescent bulbs.

### High quality light

- Designed for the comfort of your eyes
- True incandescent-like warm white light

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

### Create the right light for your home

- Perfect for decorative fixtures

### High quality LED light that lasts for decades

- Light that shows true colors

# Highlights

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## True incandescent-like warm white light



This bulb has a color temperature of 2700K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2700K light is ideal for home lighting design.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## Perfect for decorative fixture



Contemporary lighting in Philips LED lustres for use in decorative fixtures such as chandeliers, ceiling fans, vanity strips, and post lights.

## Light that shows true colors



See the true colors of your clothes when you select an outfit from your wardrobe – you can pair a red dress and red shoes with confidence and be sure the colors match perfectly.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Bulb Finish: Clear
- Dimmable: No

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

**Extra feature/accessory incl.**

- LED integrated: Yes

**Light characteristics**

- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 330 lm
- Luminous Efficacy (rated) (Nom): 82

**Miscellaneous**

- EyeComfort: Yes
- LED Innovations: EyeComfort

**Packaging information**

- EAN: 046677572501
- EOC: 572503
- Product title:  
4T10/SPC/927/E26/CL/ND 1PF

**Power consumption**

- Energy Star Certified: No
- Power factor: 0.5
- Voltage: AC 120 V
- Wattage equivalent: 40
- Power: 4

**Product dimensions and weight**

- Overall height: 3/4 inch
- Overall length: 3/4 inch
- Overall width: 1/8 inch

**Technical specifications**

- Frequency: 60
- Bulb technology: LED
- Light color: Warm white light
- can it be used in closed luminaires:  
Yes

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems:  
Not applicable

**Packaging dimensions and weight**

- EAN/UPC - product: 046677572501
- Net weight: 0.05 kg
- Gross weight: 0.08 kg
- Height: 22.5 cm
- Length: 4.6 cm
- Width: 7.5 cm



Issue date: 2026-05-14  
Version: 0.140

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)