

PHILIPS

Reflector 90W
PAR38 E26 x2

LED

5000K

900lm

11000h

046677573225



State-of-the-art LED for the home

Philips LED PAR spot light lamp are a long lasting, energy efficient replacement for halogen spots. They have a bright white light and are ideal for general and flood lighting.

Specifications

Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Directional reflector
- Socket: E26
- Type of glass: Clear
- Bulb Finish: Clear
- Dimmable: No
- Bulb Material: Glass

Bulb dimensions

- Height: 12.9 cm
- Width: 12.2 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 11,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 40 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 5000 K
- Nominal luminous flux: 900 lm
- Warm-up time to 60% light: instant full light
- Color Code: 950 | CCT of 5000K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 90 lm/W

Packaging information

- EAN: 046677573225
- EOC: 573220
- Product title:
10PAR38/950/G/E26/F40/ND/ULW
T20 4/2CT

Power consumption

- Energy Star Certified: No
- Power factor: 0.7
- Voltage: AC 120 V
- Wattage: 10 W
- Wattage equivalent: 90 W

Product dimensions and weight

- Length: 12.9 cm

Rated values

- Rated peak intensity: 1533 cd

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677573225
- Net weight: 0.64 kg
- Gross weight: 0.76 kg
- Height: 20.9 cm
- Length: 13 cm
- Width: 23.5 cm
- Material number (12NC):
929001949663



Issue date: 2024-06-17
Version: 0.56

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com