

PHILIPS

Filament Bulb Clear
60W A19 E26


UltraEfficient

3000K

810lm

50000h

046677581329



Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your clear incandescent bulbs.

Choose for a sustainable solution

- Better for your wallet and your planet
- Long life bulb - Lasts up to 50 years

Highlights

Saving up to 90% energy

LED technology saves up to 90% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

Long life bulb - Lasts up to 50 years

With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

Specifications

Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Type of glass: Clear
- Bulb Finish: Clear
- Dimmable: No
- Bulb Material: Glass

Bulb dimensions

- Height: 11 cm
- Width: 6 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 100,000
- Nominal lifetime: 50,000 hour(s)

Light characteristics

- Beam angle: / degree(s)
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Nominal luminous flux: 810 lm
- Warm-up time to 60% light: instant full light
- Color Code: 930 | CCT of 3000K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: UltraEfficient, EyeComfort

Other characteristics

- Efficacy: 180 lm/W

Packaging information

- EAN: 046677581329
- EOC: 581322
- Product title: 4.5A19/UE/930/CL/G/E26/ND 1PF/4 T20

Power consumption

- Energy Star Certified: No
- Power factor: 0.7
- Voltage: AC 120 V
- Wattage: 4.5 W
- Wattage equivalent: 60 W

Product dimensions and weight

- Length: 11 cm

Rated values

- Rated peak intensity: / cd

Technical specifications

- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677581329
- Net weight: 0.04 kg
- Gross weight: 0.07 kg
- Height: 14.6 cm
- Length: 7.5 cm
- Width: 6.5 cm
- Material number (12NC): 929003579823



Issue date: 2024-04-11
Version: 0.90

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com