



Motion Sensor

The WiZ wireless indoor motion sensor makes automating your lights as easy as walking past — and turns them off when you're gone. Place the sensor, which includes a battery, in an entrance or hallway and set it to turn the lights on or off to your desired settings at certain times.


PRODUCT HIGHLIGHTS

- Battery operated
- IP20/Plastic/White
- Works with all Connected by WiZ products



Easy wireless installation

Battery-powered, no wire necessary. Make it a quick and easy install with screws on the ceiling / wall, or simply leave it on a desk.



Flexible motion settings for your convenience

Set your lights to turn on a preferred brightness or specific mode, such as nightlight or daylight. You can configure an action for your lights, with a specified delay, and when no motion is detected.



Set the right light for the right time

Set sensors to activate your favorites light modes at different times during the day, by setting specific Rhythms for a room in the WiZ app.



Compatible with all "Connected by WiZ" lights

This WiZ control accessory is designed to control all kinds of lights in the WiZ ecosystem. You can use it to control any lights from any brand as long as it's "Connected by WiZ."



Trigger lights with motion

Set your lights to turn on/off or change brightness and color whenever they detect any motion. This sensor connects directly to your WiZ lights and works even when the Wi-Fi is down.



Wide connection range of 15m / 50ft

This motion sensor connects with WiZ lights placed within a range of up to 15 meters or 50 feet in a normal indoor environment with partitions and walls.



SPECIFICATIONS

DESIGN AND FINISHING

Color: White
Material: Plastic

EXTRA FEATURE/ACCESSORY INCL.

Batteries included: Yes
Detection Area: 0 - 3 m
Control Distance: 15 m

POWER CONSUMPTION

Voltage: 3 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.103 kg
Overall height: 2 inch
Overall length: 2-1/2 inch
Overall width: 2-1/2 inch

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Battery type: AA
IP code: IP20 | Finger-protected
Class of protection: Class III - Safe
Extra Low Voltage

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677603472
Net weight: 0.1 kg
Gross weight: 0.14 kg
Height: 16 cm
Length: 7 cm
Width: 7 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.