

# PHILIPS

Pedestal/Pathway  
Light

Outdoor Solar

7000K

Black

Sensor

046677607173



## Durable and bright

Powered Waterproof Wall-Mounted Floodlight

**Advanced LED light**

- High quality LED light

**Designed for outdoors**

- IP65 weatherproof rated

# Highlights

## High quality LED light



These LED lights use a unique technology developed by Philips. They turn on instantly and produce optimal light output that brings out the vivid colors in your garden.

## IP65 weatherproof rated

An IP rating contains two digits which refer to protection against solids, such as dust, or liquids, such as rain. IP65 means that these light fixtures are protected against water splashed from any direction and are suitable for outdoor use.

# Specifications

## Design and finishing

- Color: Black
- Material: Plastic

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Anti rust anti dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: Yes
- Solar Energy: Yes
- Centerpiece: No

## Light characteristics

- Color rendering index (CRI): 70
- Color temperature: 7000 K

## Miscellaneous

- Especially designed for: Garden, Patio
- Style: Modern
- Type: Pedestal/Pathway Lights
- EyeComfort: No
- Extra Features: Sensor

## Power consumption

- Power: 12.5

## Product dimensions and weight

- Net weight: 0.698 kg
- Overall height: 4-3/4 inch
- Overall length: 10-5/8 inch
- Overall width: 5-1/8 inch

## Service

- Warranty: 1 year(s)

## Technical specifications

- Total lumen output fixture: 1200
- Bulb technology: LED
- Light color: Daylight Deluxe
- Mains power: DC 4
- Fixture dimmable: No
- IP code: IP65
- Class of protection: Class III - Safe Extra Low Voltage
- Light source replaceable: No

## The bulb

- Software upgradable: No

## What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

**Packaging dimensions and weight**

- EAN/UPC - product: 046677607173
- Net weight: 0.7 kg
- Gross weight: 1 kg
- Height: 11 cm
- Length: 16.3 cm
- Width: 23.3 cm



Issue date: 2026-06-10  
Version: 0.217

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)