

PHILIPS

Bulb 75W A19 E26
x2

LED

2700/3000/3500/4000/5000
K

1100lm

15000h

Dimming

046677607586



Selectable colour temperatures help you to make the right choice

Enjoy 5 possible light colors in one product. Change the color of your light easily with by switching the button on the product.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Bulb Finish: Frosted
- Dimmable: Yes
- Bulb Material: Plastic

Bulb dimensions

- Height: 4-9/16 inch
- Width: 2-3/8 inch

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 220
- Color rendering index (CRI): 90
- Color temperature: 2700-3000-3500-4000-5000 K
- Nominal luminous flux: 1100 lm
- Luminous Efficacy (rated) (Nom): 100

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

Packaging information

- EAN: 046677607586
- EOC: 607580
- Product title: 11A19/DipS/5CCT/FR/P/E26/DIM/T20 2PF

Power consumption

- Energy Star Certified: No
- Power factor: 0.7
- Voltage: AC 120 V
- Wattage equivalent: 75
- Power: 11

Product dimensions and weight

- Length: 4-9/16 inch
- Overall height: 4-9/16 inch
- Overall length: 4-9/16 inch
- Overall width: 2-3/8 inch

Technical specifications

- Frequency: 60
- Bulb technology: LED
- can it be used in closed luminaires: No

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 046677607586
- Net weight: 0.09 kg
- Gross weight: 0.13 kg
- Height: 17.1 cm
- Length: 6.6 cm
- Width: 13.1 cm



Issue date: 2026-05-13
Version: 0.265

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com